

## SmartRack 9U Low-Profile Switch-Depth-Plus Wall-Mount Mini Rack Enclosure, Wide, Acrylic Window

MODEL NUMBER: SRW9UDPGVRT



9U rack cabinet with extra width for convenient cable management houses, organizes and secures standard 19 in. rack equipment.

### Features

**Space-Saving 9U Wall-Mount Enclosure Houses 19 in. Rack Equipment up to 20.5 in. Deep** This SmartRack® cabinet is designed to house 9U of equipment, such as network switches and patch panels. It's recommended for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 pounds (90.7 kg).

**Lockable for Simple and Secure Equipment Access** The front door and side panels lock securely to help prevent damage, tampering or theft. The reversible front door can open left or right by rotating the cabinet 180 degrees before mounting. Convenient top and bottom access ports allow easy cable routing through the cabinet.

**Generous Airflow Keeps Equipment Cool** Round ports built into the top, bottom and both sides are designed for optional ventilation fans (such as SRFANWM, sold separately) that keep your equipment cool and functioning at their peak.

**Designed with Extra Width for Easier Cable Access and Better Airflow** The SRW9UDPGVRT is three inches wider than standard-width wall-mount racks. Combined with two vertical cable managers with pre-installed finger ducts in front and two cable pass-through ports on top, the extra width provides convenient cable management along the front of the rack. This allows easier cable access from the front and increases airflow by minimizing rear cable clutter that can obstruct vents. Cutouts on top of the rack can be used to secure cable bundles.

**Shatter-Resistant Clear Acrylic Front Window** The front door features a shatter-resistant clear acrylic window that lets you monitor equipment readouts without unlocking the enclosure. Not only does the window help prevent equipment tampering and reduce acoustic noise, it also adds visual flair to your IT installation.

**Easy Enclosure and Equipment Installation** This 9U server rack comes fully assembled and ready to mount to the wall with user-supplied hardware. The side panels can be removed for convenient installation, maintenance and replacement of equipment. Front and rear mounting rails adjust independently to accommodate equipment up to 20.5 inches deep, including network switches and patch

### Highlights

- 9U rack constructed from powder-coated steel that stands up to tough environments
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Extra 3 in. width and internal cable managers cut down on rear cord clutter
- Ships fully assembled for immediate wall-mounting with user-supplied hardware
- Provides physical equipment and media security required for PCI DSS compliance

### Applications

- Store and organize rack-mount equipment in a network wiring closet, retail location, classroom, office or other area where you need equipment to be secure

### Package Includes

- SRW9UDPGVRT SmartRack 9U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet
- (22) M6 screws
- (22) M6 cage nuts
- (22) M6 cup washers
- (22) 12-24 screws
- Removable mounting plate
- Vertical cable management fingers
- (3) Mounting plate screws
- (2) Keys
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

panels.

**Meets Payment Card Industry Standards**The SRW9UDPGVRT provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance.

## Specifications

OVERVIEW	
UPC Code	037332214263
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	9U
Rack Depth	Shallow
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	23.03 x 24.40 x 32.28
Shipping Dimensions (hwd / cm)	58.50 x 61.98 x 81.99
Shipping Weight (lbs.)	58.86
Shipping Weight (kg)	26.70
Unit Dimensions (hwd / in.)	19.830 x 29.622 x 21.710
Unit Dimensions (hwd / cm)	50.37 x 75.24 x 55.14
Unit Weight (lbs.)	53.130
Unit Weight (kg)	24.10
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames



Powering Business Worldwide

TRIPP LITE  
SERIES

Built-in Cable Management	Yes
Extra Wide	No
Pre-Installed Casters	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS; EIA/ECA-310-E
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.