

SmartRack 9U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet, White

MODEL NUMBER: SRW9UDPW



Secures and organizes 9U of rack equipment up to 20.5 in. deep in network closets and other locations with limited floor space.

Features

Space-Saving 9U Wall-Mount Enclosure Houses 19 in. Rack Equipment up to 20.5 in. Deep This SmartRack® EIA-310 cabinet is designed to house 9U of equipment, such as network switches and patch panels. It's recommended for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable white powder-coated finish, the cabinet has a maximum load capacity of 200 pounds.

Lockable for Simple and Secure Equipment Access The front door and removable side panels lock securely to help prevent damage, tampering or theft. The reversible front door can open left or right by rotating the cabinet 180 degrees before mounting. Convenient top and bottom access ports allow easy cable routing through the cabinet.

Generous Airflow Keeps Equipment Cool The front door and both sides are ventilated to ensure a constant flow of air that cools rack-mount equipment and helps prevent overheating that can lead to costly downtime. Round ports built into the top and bottom are designed for optional ventilation fans (such as Tripp Lite's SRFANWM, sold separately) that increase airflow and expel heat.

Easy Enclosure and Equipment Installation This 9U server rack comes fully assembled and ready to mount to the wall with user-supplied hardware. The side panels can be removed for convenient installation, maintenance and replacement of equipment. Front and rear mounting rails adjust independently to accommodate equipment up to 20.5 inches deep, including network switches and patch panels. Hardware for mounting equipment inside the rack is included.

Make It a Mobile Rack Cabinet to Take It Where Best Needed Instead of mounting the 9U enclosure on a wall, you may install Tripp Lite's optional SRCASTER rolling caster kit (sold separately) to smoothly wheel the rack along the floor to its destination.

Meets Payment Card Industry Standards The SRW9UDPW provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance.

Highlights

- 9U rack constructed from powder-coated steel that stands up to tough environments
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Flow-through ventilation all around keeps equipment cool to maintain top performance
- Ships fully assembled for immediate wall-mounting with user-supplied hardware
- Provides physical equipment and media security required for PCI DSS compliance

Applications

- Store and organize rack-mount equipment in a network wiring closet, retail location, classroom, office or other area where you need equipment to be secure

Package Includes

- SRW9UDPW SmartRack 9U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet
- (18) M6 screws
- (18) M6 cage nuts
- (18) M6 cup washers
- (18) 12-24 screws
- Removable mounting plate
- (3) Mounting plate screws
- (2) Keys
- Owner's manual

Specifications



OVERVIEW	
UPC Code	037332256065
Device Compatibility	Patch Panel; Network Switch
Rack Type	Enclosure
PHYSICAL	
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Color	White
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Rack Height	9U
Shipping Dimensions (hwd / in.)	24.41 x 28.75 x 26.57
Shipping Weight (kg)	22.23
Unit Dimensions (hwd / cm)	50.37 x 59.99 x 55.14
Unit Dimensions (hwd / in.)	19.83 x 23.62 x 21.71
Unit Weight (kg)	23.50
Unit Weight (lbs.)	51.8
Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Rack Depth	Shallow
Number of Vertical Mounting Rails	4
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
Built-in Cable Management	No
Extra Wide	No
STANDARDS & COMPLIANCE	
Certifications	EIA-310-E; IP20 Protection Rating
Approvals	RoHS
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	5-year limited warranty
----------------------------------------	-------------------------

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>