

## Universal Coupler Kit for Wire Mesh Cable Trays, 50 Pack

MODEL NUMBER: SRWBUNVCPLR



Securely connects sections of wire mesh cable tray in an intersection or sweep in your data center or network closet.

### Features

#### High-Resiliency Couplers Help You Create Custom Cable Management Schemes

The SmartRack® SRWBUNVCPLR includes 50 black powder-coated metal couplers, each with an M6 flange nut and M6 x 20 carriage bolt for easy installation with your wire mesh cable tray. By creating a secure connection point between two intersecting sections of cable tray in your server room or data center, these couplers help you create sweeps and 90-degree intersections that guide the direction of cabling to your liking.

### Highlights

- Connects wire mesh cable tray sections in a ceiling, floor or wall installation
- Allows you more flexibility in routing custom cable management applications
- Made from resilient black powder-coated metal designed to last
- Includes 50 couplers, each with a mounting nut and bolt for quick installation

### Applications

- Organize a wire mesh cable tray system with intersecting sections along the wall, floor or ceiling of your data center

### System Requirements

SRWB sectional pieces

### Package Includes

- (50) Couplers
- (50) M6 flange nuts
- (50) M6 x 20 carriage bolts
- Installation guide

## Specifications

OVERVIEW	
UPC Code	037332240361
Product Type	Coupler
Accessory Type	Cable Management Accessories
Cable Management System Component Type	Coupler
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Shipping Dimensions (hwd / in.)	1.90 x 3.40 x 12.40
Shipping Weight (kg)	2.04
Unit Dimensions (hwd / in.)	0.232 x 1.232 x 0.708
Unit Dimensions (hwd / cm)	0.59 x 3.13 x 1.800



Powering Business Worldwide

TRIPP LITE  
SERIES

Unit Weight (lbs.)	2.00
Unit Weight (kg)	0.91
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.