

SmartRack 2U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRWF2U36**



Wall-mount cabinet secures and organizes 2U of 19-inch rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 36 inches deep, but extends less than 5 inches from wall.

Description

The SRWF2U36 SmartRack 2U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 lbs (68 kgs).

Because the low-profile cabinet mounts vertically, it extends less than five inches from the wall while housing equipment up to 36 inches deep, including 1U servers, UPS systems, battery packs and switches. In addition to 2U of rack space in the primary mounting area, it also includes a slide-out 1U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The front door locks securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF2U36 comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

Features

Saves Valuable Workspace Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
Houses EIA-standard 19 in. rack equipment in 2U of space
Low-profile vertical-mount cabinet extends less than 5 in. from the wall while housing equipment up to 36 in. deep, including 1U servers, UPS systems, battery packs and switches
Also includes a slide-out 1U mounting bracket at the top of the

Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 2U of 19 in. rack equipment up to 36 in. deep
- Includes additional 1U of space for patch panels
- Ships fully assembled for quick installation

Package Includes

- SRWF2U36 SmartRack 2U Low-Profile Vertical-Mount Server-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



enclosure for patch panels up to 2.5 in. deepMaximum load capacity of 150 lbs (68 kgs)
Keeps Important Equipment SecureReversible front door locks securely to help prevent damage, tampering or theftVented cabinet keeps equipment coolConvenient ports with removable covers allow cable routing through top and bottom
Easy Enclosure and Equipment InstallationShips fully assembled for quick installationWall-mounting holes spaced 16 in. apart for standard wall stud placementRails adjust easily—unscrew them, slide them to desired depth, and screw them back inThreaded mounting holes support M6 or 12-24 mountingRack spaces marked for easy reference
Meets Payment Card Industry StandardsProvides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332190604
Device Compatibility	Network Switch; Patch Panel; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	91.44
Maximum Device Depth (in.)	36
Maximum Device Depth (mm)	914
Rack Height	2U
Shipping Dimensions (hwd / cm)	23.98 x 78.99 x 122.00
Shipping Dimensions (hwd / in.)	9.44 x 31.10 x 48.03
Shipping Weight (kg)	29.03
Shipping Weight (lbs.)	64.00
Unit Dimensions (hwd / cm)	109.22 x 65.02 x 11.43
Unit Dimensions (hwd / in.)	43 x 25.6 x 4.5
Unit Weight (kg)	26.70
Unit Weight (lbs.)	58.86
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Rack Depth	Standard
Number of Vertical Mounting Rails	2
SPECIAL FEATURES	
Built-in Cable Management	No
Extra Wide	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
Certifications	EIA-310-E; IP20 Protection Rating
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>