

## SmartRack 4U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRWF4U**



Wall-mount cabinet secures and organizes 4U of 19-inch rack equipment in network wiring closets and other locations with limited floor space. Houses equipment up to 20 inches deep, but extends just 8 inches from wall.

### Description

The SRWF4U SmartRack 4U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 150 lbs (68 kgs).

Because the low-profile cabinet mounts vertically, it extends only eight inches from the wall while housing equipment up to 20 inches deep, including network switches and patch panels. In addition to 4U of rack space in the primary mounting area, it also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 inches deep.

The top panel and front door lock securely to help prevent damage, tampering or theft. The cabinet is vented, which allows air to flow freely and keep equipment cool. The reversible front door can open left or right. Convenient top and bottom ports allow easy cable routing.

The SRWF4U comes fully assembled and ready to mount to the wall. Equipment installation is easy with threaded mounting holes and hardware that support M6 or 12-24 mounting.

### Features

**Saves Valuable Workspace** Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way  
Houses EIA-standard 19 in. rack equipment in 4U of space  
Low-profile vertical-mount cabinet extends

### Highlights

- Maximum load capacity of 150 lbs (68 kgs)
- Locking steel cabinet vented to keep equipment cool
- Secures 4U of 19 in. rack equipment up to 20 in. deep
- Includes additional 2U of space for patch panels
- Ships fully assembled for quick installation

### Package Includes

- SRWF4U SmartRack 4U Low-Profile Vertical-Mount Switch-Depth Wall-Mount Rack Enclosure Cabinet
- (12) M6 screws
- (12) M6 cup washers
- (12) 12-24 screws
- (2) Keys
- Owner's manual



only 8 in. from the wall while housing equipment up to 20 in. deep, including network switches and patch panels Also includes a slide-out 2U mounting bracket at the top of the enclosure for patch panels up to 2.5 in. deep Maximum load capacity of 150 lbs (68 kgs)

**Keeps Important Equipment Secure** Top panel and reversible front door lock securely to help prevent damage, tampering or theft Vented cabinet keeps equipment cool Convenient ports with removable covers allow cable routing through top and bottom

**Easy Enclosure and Equipment Installation** Ships fully assembled for quick installation Wall-mounting holes spaced 16 in. apart for standard wall stud placement Rails adjust easily—unscrew them, slide them to desired depth, and screw them back in Threaded mounting holes support M6 or 12-24 mounting Rack spaces marked for easy reference

**Meets Payment Card Industry Standards** Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

## Specifications

OVERVIEW	
UPC Code	037332190611
Device Compatibility	Patch Panel; Network Switch
Rack Type	Enclosure
PHYSICAL	
Color	Black
Maximum Device Depth (cm)	50.80
Maximum Device Depth (in.)	20
Maximum Device Depth (mm)	508
Rack Height	4U
Shipping Dimensions (hwd / cm)	33.99 x 78.99 x 87.00
Shipping Dimensions (hwd / in.)	13.38 x 31.10 x 34.25
Shipping Weight (kg)	25.40
Shipping Weight (lbs.)	56.00
Unit Dimensions (hwd / cm)	73.15 x 65.02 x 20.32
Unit Dimensions (hwd / in.)	28.8 x 25.6 x 8
Unit Weight (kg)	27.30
Unit Weight (lbs.)	60.18
Weight Capacity - Stationary (kg)	68
Weight Capacity - Stationary (lbs.)	150
Rack Depth	Shallow
Number of Vertical Mounting Rails	2
SPECIAL FEATURES	
Built-in Cable Management	No



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Extra Wide	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	EIA-310-E; IP20 Protection Rating
Approvals	RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>