

SmartRack 4U Low-Profile Vertical-Mount Vented Wall-Mount Mini Rack Enclosure, Black

MODEL NUMBER: SRWO4UBRKT



Wall-mount cabinet secures and organizes 4U of rack equipment in confined spaces, such as classrooms and back offices.

Features

4U Vented Rack Enclosure Ideal for Housing Network Equipment in Small Spaces

This SmartRack® cabinet is recommended for wiring closets, retail locations, classrooms, back offices and other confined spaces where you need server or network equipment to be organized and out of the way. Made from heavy-duty cold-rolled steel with a durable black powder-coated finish, the vertical-mount SRWO4UBRKT has a maximum load capacity of 75 pounds (34 kilograms).

Low-Profile Design Accommodates Switches, Panels and Other Standard Rack Equipment

The 4U cabinet extends less than eight inches (20.3 centimeters) from the wall while housing network components up to 19 inches (48.3 centimeters) deep, including switches and patch panels. It is vented on both sides to allow air to flow freely and keep equipment cool. The top and bottom are open for convenient cable routing and access.

Easy Enclosure Deployment and Equipment Installation

The SRWO4UBRKT comes assembled (except for the front panel) and ready to mount to a wall or beneath a desk. Rear keyhole mounting slots are spaced 16 inches (40.6 centimeters) apart to match standard wall studs. Hardware is included for equipment installation.

Highlights

- Low-profile cabinet extends less than 8 in. from wall to save space in small areas
- Heavy-duty cold-rolled steel construction with maximum load capacity of 75 lb.
- Vented design maximizes airflow to protect equipment against excessive heat
- Keyhole mounting slots spaced 16 in. apart to match standard wall-stud placement
- Includes equipment-mounting hardware for convenient installation

Package Includes

- SRWO4UBRKT 4U Low-Profile Vertical-Mount Vented Wall-Mount Mini Rack Enclosure
- Front panel
- (32) M6 screws
- (32) M6 cup washers
- (32) M6 cage nuts
- Assembly instructions

Specifications

| OVERVIEW | |
|----------------------|------------------------------------------|
| UPC Code | 037332262998 |
| Device Compatibility | Network Switch; Patch Panel; Router; UPS |
| Rack Type | Small Enclosure |
| PHYSICAL | |

| | |
|--------------------------------------|----------------------------|
| Color | Black |
| Rack Height | 4U |
| Rack Depth | Shallow |
| Maximum Device Depth (cm) | 49.28 |
| Maximum Device Depth (in.) | 19.4 |
| Maximum Device Depth (mm) | 493 |
| Unit Dimensions (hwd / in.) | 21.467 x 20.135 x 7.953 |
| Unit Dimensions (hwd / cm) | 54.526 x 51.143 x 20.201 |
| Unit Weight (lbs.) | 15.500 |
| Unit Weight (kg) | 7.03 |
| Weight Capacity - Stationary (kg) | 34 |
| Weight Capacity - Stationary (lbs.) | 75 |
| Number of Vertical Mounting Rails | 2 |
| Assembly Required | Yes |
| FEATURES & SPECIFICATIONS | |
| Grounding Lug | N/A |
| Built-in Cable Management | No |
| Extra Wide | No |
| Pre-Installed Casters | No |
| STANDARDS & COMPLIANCE | |
| Product Compliance | EIA/ECA-310-E; REACH; RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 5-year limited warranty |