

Wall-Mount Double Shelf for IT Equipment, 20 in. Wide, Up to 250 lb. (113 kg)

MODEL NUMBER: SRWOSHELFLG



Organizes and stores IT equipment, such as routers and small switches, on the wall of your home office or network closet.

Features

The Ideal Alternative to a Wall-Mount Rack Cabinet

If you don't have enough equipment to justify the expense of a rack enclosure or you don't have the space for one in your home or office, the SRWOSHELFLG fills your needs. The heavy-duty steel unit mounts easily to the wall of your back office or closet and holds up to 250 pounds (113 kilograms) of equipment. It's recommended for network equipment, including routers, small switches, media servers and other networking components.

Designed for Convenient Cable Management and Equipment Care

The steel surfaces are smooth and the edges are rounded to reduce wear on cable jackets. Open cutouts with rubber grommets on the two shelves permit easy cable feeds to streamline installation and reduce clutter. The vented shelves allow generous airflow to keep equipment cool and functioning at their best.

Easy to Install with the Included Hardware

Mounting screws are included for mounting the SRWOSHELFLG on a wall. Rear keyhole slots are spaced 16 inches apart to match standard wall-stud placement.

Highlights

- Ideal alternative to a wall-mount rack enclosure
- Perforated shelves support maximum equipment load up to 250 lb.
- Keyhole mounting slots spaced 16 in. apart to match standard wall-stud placement
- Steel construction with smooth edges and rubber grommets for cable entry
- Designed for easy assembly using included hardware

Package Includes

- Base panel
- Right panel
- Left panel
- Rear panel
- Top shelf
- (16) M5 x 8 screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332263018
Device Compatibility	Network Switch; Router
Rack Type	Shelf
PHYSICAL	
Color	Black
Material of Construction	Steel



Powering Business Worldwide

TRIPP LITE
SERIES

Rack Height	0U
Rack Depth	Shallow
Maximum Device Depth (cm)	53.34
Maximum Device Depth (in.)	21.00
Maximum Device Depth (mm)	533
Unit Dimension Details	Vertical distance between shelves: 7.21 inches (183.13 mm)
Unit Dimensions (hwd / in.)	14.980 x 20.230 x 21.120
Unit Dimensions (hwd / cm)	38.05 x 51.38 x 53.65
Unit Weight (lbs.)	28.00
Unit Weight (kg)	12.70
Weight Capacity - Stationary (kg)	113
Weight Capacity - Stationary (lbs.)	250
Number of Shelves	2
Mounting Details	Accommodates all standard 19-inch rack-mount equipment.
Assembly Required	Yes
Cable Entry/Exit	4 cable grommets (2 large, 2 small)
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.