

Wall-Mount Shelf for IT Equipment, 20 in. Wide, Up to 200 lb. (90 kg)

MODEL NUMBER: SRWOSHELF5M



Organizes and stores IT equipment, such as routers and small switches, on the wall of your home office or network closet.

Features

The Ideal Alternative to a Wall-Mount Rack Cabinet

If you don't have enough equipment to justify the expense of a rack enclosure or you don't have the space for one in your home or office, the SRWOSHELF5M fills your needs. The heavy-duty steel unit mounts easily to the wall of your back office or closet and holds up to 200 pounds (90 kilograms) of equipment. It's recommended for network equipment, including routers, small switches, media servers and other networking components.

Designed for Convenient Cable Management and Equipment Care

The steel surfaces are smooth and the edges are rounded to reduce wear on cable jackets. Open cutouts with rubber grommets on the two shelves permit easy cable feeds to streamline installation and reduce clutter. The vented shelf allows generous airflow to keep equipment cool and functioning at their best.

Easy to Install with the Included Hardware

Mounting screws are included for mounting the SRWOSHELF5M on a wall. Rear keyhole slots are spaced 16 inches apart to match standard wall-stud placement.

Highlights

- Ideal alternative to a wall-mount rack enclosure
- Perforated shelf supports maximum equipment load up to 200 lb. (90 kg.)
- Keyhole mounting slots spaced 16 in. apart to match standard wall-stud placement
- Steel construction with smooth edges and rubber grommets for cable entry
- Designed for easy assembly using included hardware

Package Includes

- Base panel
- Right panel
- Left panel
- Rear panel
- (12) M5 x 8 screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332263001
Device Compatibility	Network Switch; Router
Rack Type	Shelf
PHYSICAL	
Color	Black



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Material of Construction	Steel
Rack Height	0U
Rack Depth	Shallow
Maximum Device Depth (cm)	43.18
Maximum Device Depth (in.)	17.00
Maximum Device Depth (mm)	432
Unit Dimensions (hwd / in.)	14.98 x 20.23 x 17.12
Unit Dimensions (hwd / cm)	38.05 x 51.38 x 43.48
Unit Weight (lbs.)	20.00
Unit Weight (kg)	9.07
Weight Capacity - Stationary (kg)	16
Weight Capacity - Stationary (lbs.)	35.00
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Extra Wide	No
Grounding Lug	No
Built-in Cable Management	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>