

Wall-Mount Shelf for IT Equipment, 20 in. Wide, Up to 200 lb. (90 kg)

MODEL NUMBER: SRWOSHELF5M



Organizes and stores IT equipment, such as routers and small switches, on the wall of your home office or network closet.

Features

The Ideal Alternative to a Wall-Mount Rack Cabinet

If you don't have enough equipment to justify the expense of a rack enclosure or you don't have the space for one in your home or office, the SRWOSHELF5M fills your needs. The heavy-duty steel unit mounts easily to the wall of your back office or closet and holds up to 200 pounds (90 kilograms) of equipment. It's recommended for network equipment, including routers, small switches, media servers and other networking components.

Designed for Convenient Cable Management and Equipment Care

The steel surfaces are smooth and the edges are rounded to reduce wear on cable jackets. Open cutouts with rubber grommets on the two shelves permit easy cable feeds to streamline installation and reduce clutter. The vented shelf allows generous airflow to keep equipment cool and functioning at their best.

Easy to Install with the Included Hardware

Mounting screws are included for mounting the SRWOSHELF5M on a wall. Rear keyhole slots are spaced 16 inches apart to match standard wall-stud placement.

Highlights

- Ideal alternative to a wall-mount rack enclosure
- Perforated shelf supports maximum equipment load up to 200 lb. (90 kg.)
- Keyhole mounting slots spaced 16 in. apart to match standard wall-stud placement
- Steel construction with smooth edges and rubber grommets for cable entry
- Designed for easy assembly using included hardware

Package Includes

- Base panel
- Right panel
- Left panel
- Rear panel
- (12) M5 x 8 screws
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332263001
Device Compatibility	Network Switch; Router
Rack Type	Shelf
PHYSICAL	
Color	Black
Material of Construction	Steel



Powering Business Worldwide



Rack Height	0U
Rack Depth	Shallow
Maximum Device Depth (cm)	43.18
Maximum Device Depth (in.)	17.00
Maximum Device Depth (mm)	432
Unit Dimensions (hwd / in.)	14.980 x 20.230 x 17.120
Unit Dimensions (hwd / cm)	38.05 x 51.38 x 43.48
Unit Weight (lbs.)	200
Unit Weight (kg)	90.72
Weight Capacity - Stationary (kg)	16
Weight Capacity - Stationary (lbs.)	35.00
Assembly Required	Yes
Cable Entry/Exit	4 cable cutouts with rubber grommets
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Locking	No
Pre-Installed Casters	No
Outdoor Use	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://triplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.