

47U Deep & Wide Server Rack, Euro-Series - 1200 mm Depth, 800 mm Width, Doors & Side Panels Included

MODEL NUMBER: SRX47UBDPWD



Extra-deep and -wide 47U rack enclosure houses, organizes and secures rack equipment in high-density server and IT networking areas.

Features

Extra-Deep and -Wide Server Rack Accommodates 47U of Rack Equipment This SmartRack® 47U server rack is designed for network wiring closets, retail locations, classrooms, back offices and other areas with essential rack-mount IT equipment. It is 800 millimeters wide and 1200 millimeters deep to support mounting of equipment up to 1050 millimeters in depth. This allows more room in the rear for removing hot-swap power supplies from mounted devices and extra room along the sides for cable management and 0U PDU mounting.

Designed to Stand Up to Harsh Environments, Such as Warehouses Constructed from heavy-duty steel with a durable black powder-coated finish, the SRX47UBDPWD has a maximum stationary load capacity of 1360 kilograms and a maximum rolling load capacity of 1020 kilograms.

Keeps Important Equipment Secure The reversible front door, split rear doors and half-size side panels lock securely to help prevent damage, tampering or theft. The doors, side panels and top panel are designed for quick release, making it easy to access connected equipment and cabling with little effort. Convenient top access ports and an open bottom allow easy cable routing through the cabinet. The vented doors allow generous airflow from front to rear to keep your equipment cool and functioning at their peak.

Easy Enclosure and Equipment Installation This 47U server cabinet comes fully assembled for quick and easy deployment with pre-installed casters that let you maneuver it over a level, smooth, stable surface and through a standard two-meter doorway into position, where it can be stabilized by adjusting the levelers. Four mounting rails adjust in 6.35-millimeter increments to accommodate equipment up to 1050 millimeters deep. Toolless 0U mounting rails allow quick installation of up to four compatible PDUs and vertical cable managers.

Designed for Baying Multiple Enclosures in a Row Built-in baying brackets allow the combination of two or more rack cabinets in a row. Center-to-center width can be set at 800 millimeters.

Meets Payment Card Industry Standards The SRX47UBDPWD provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance. This is essential for companies that process, store and/or transmit credit card information.

Highlights

- 47U rack constructed from powder-coated steel that stands up to tough environments
- 800 mm wide to allow side cable management and PDU mounting
- Doors and side panels lock securely to help prevent damage, tampering or theft
- Ships fully assembled for quick deployment on pre-installed casters
- Mounting rails accept standard rack equipment up to 1050 mm deep

Applications

- Store and organize rack-mount equipment, cable managers and 0U PDUs in a network closet, data center or other area where you need components to be secure

Package Includes

- SRX47UBDPWD 47U Server Rack
- (4) Side panels
- (4) Side panel locks
- (2) Keys
- (50) M6 screws
- (50) M6 washers
- (50) M6 cage nuts
- Owner's manual

Specifications



OVERVIEW	
UPC Code	037332224545
Device Compatibility	Patch Panel; Network Switch; UPS; Server
Rack Type	Enclosure
PHYSICAL	
Color	Black
Factory Preset Rack Depth (in.)	28.125
Factory Preset Rack Depth (cm)	71.4
Factory Preset Rack Depth (mm)	714
Maximum Device Depth (cm)	104.98
Maximum Device Depth (in.)	41.33
Maximum Device Depth (mm)	1,050
Minimum Device Depth (cm)	10.16
Minimum Device Depth (in.)	4
Minimum Device Depth (mm)	102
Rack Height	47U
Shipping Dimensions (hwd / cm)	246.89 x 85.00 x 128.83
Shipping Dimensions (hwd / in.)	97.20 x 33.46 x 50.72
Shipping Weight (kg)	206.96
Shipping Weight (lbs.)	456.27
Unit Dimensions (hwd / cm)	221,49 x 80,00 x 124,61
Unit Dimensions (hwd / in.)	87.200 x 31.496 x 49.060
Unit Weight (kg)	185.20
Unit Weight (lbs.)	408.300
Weight Capacity - Rolling (kg)	1,021
Weight Capacity - Rolling (lbs.)	2250
Weight Capacity - Stationary (kg)	1,361
Weight Capacity - Stationary (lbs.)	3000
Rack Depth	Deep
Number of Vertical Mounting Rails	4
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
Built-in Cable Management	No



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Extra Wide	Yes
STANDARDS & COMPLIANCE	
Certifications	UL60950; RoHS, CE; IP20 Protection Rating
Approvals	EIA/ECA-310-E
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>