

SmartOnline 200-240V 10kVA 9kW UPS Spare / Redundant Power Module, 3U Rack/Tower

MODEL NUMBER: **SU10000RT3UPM**



Highlights

- 10,000VA on-line 3U rack/tower hot-swappable power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving SU10000RT3UPM

Package Includes

- SU1000RT3UPM POWER MODULE ONLY (3u)

Description

10,000 VA (10kVA) on-line, double-conversion UPS power module for spare or redundant UPS configurations involving SU10000RT3U, SU10000RT3UG, SU10000RT3U2TF, SU10KRT3U, SU10KRT3UHV, SU20KRT, SU20KRT-1TF, SU20KRTG, SU20KRTHW UPS bundles. POWER MODULE ONLY.

Features

- 10,000 VA (10kVA) on-line, double-conversion UPS power module for spare or redundant UPS configurations involving select 10 and 20kVA configurations
- POWER MODULE ONLY

Specifications

OVERVIEW	
UPC Code	037332127006
Accessory Type	Power Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC
OUTPUT	
Output Capacity (VA)	10000
Output Capacity (kVA)	10
Output Capacity (Watts)	9000

Output Capacity (kW)	9
Power Factor	0,9
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	200V; 208V; 220V; 230V; 240V
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
PHYSICAL	
Primary Form Factor	Rackmount
Minimum Required Rack Depth (cm)	73.66
Minimum Required Rack Depth (inches)	29
Primary UPS Depth (mm)	656
Primary UPS Height (mm)	131
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	9.20 x 23.10 x 39.00
Shipping Dimensions (hwd / cm)	23.37 x 58.67 x 99.06
Shipping Weight (lbs.)	73.75
Shipping Weight (kg)	33.45
Unit Dimension Details	3U power module component only
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	13.06 x 44.45 x 65.58
UPS Power Module Dimensions (hwd, in.)	5.14 x 17.5 x 25.82
UPS Power Module Weight (kg)	20.32
UPS Power Module Weight (lbs.)	44.8
Unit Dimensions (hwd / in.)	5.140 x 17.500 x 25.820

COMMUNICATIONS	
Communications Interface	DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface; USB (HID enabled)
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC Part 15 Class A (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty