

SmartOnline 12kVA 8.4kW Spare/Replacement UPS Power Module, 4U Rack/Tower - for SU12000RT4U or SU12000RT4UHW

MODEL NUMBER: **SU12000RT4UPM**



Highlights

- 12,000VA on-line 4U replacement power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving SU12000RT4U or SU12000RT4UHW

Package Includes

- SU12000RT4UPM POWER MODULE ONLY (4U)

Description

12,000 VA (12kVA) on-line, double-conversion UPS replacement power module for UPS configurations involving SU12000RT4U or SU12000RT4UHW

Features

- 12,000VA on-line 4U replacement power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving SU12000RT4U or SU12000RT4UHW
- REPLACEMENT POWER MODULE ONLY

Specifications

| OVERVIEW | |
|-------------------------------|--------------|
| UPC Code | 037332153036 |
| OUTPUT | |
| Output Volt Amp Capacity (VA) | 12000 |
| Output kVA Capacity (kVA) | 12 |
| Output Watt Capacity (Watts) | 8400 |
| Crest Factor | 3:1 |
| Frequency Compatibility | 50 / 60 Hz |
| Output AC Waveform (AC Mode) | Sine wave |



| | |
|--|--|
| Output AC Waveform (Battery Mode) | Pure Sine wave |
| PHYSICAL | |
| Primary Form Factor | Rackmount |
| Primary UPS Depth (mm) | 706 |
| Primary UPS Height (mm) | 178 |
| Primary UPS Width (mm) | 445 |
| Shipping Dimensions (hwd / cm) | 34.29 x 59.69 x 82.55 |
| Shipping Dimensions (hwd / in.) | 13.50 x 23.50 x 32.50 |
| Shipping Weight (kg) | 58.06 |
| Shipping Weight (lbs.) | 128.00 |
| Unit Dimension Details | 4U power module component only. |
| UPS Housing Material | Steel |
| UPS Power Module Dimensions (hwd, cm) | 17.78 x 44.45 x 70.61 |
| UPS Power Module Dimensions (hwd, in.) | 7 x 17.5 x 27.8 |
| UPS Power Module Weight (kg) | 39.01 |
| UPS Power Module Weight (lbs.) | 86 |
| COMMUNICATIONS | |
| Communications Interface | Contact closure; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface |
| STANDARDS & COMPLIANCE | |
| UPS Certifications | Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to UL1778 (USA) |
| WARRANTY | |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>