

SmartOnline 4U 16kVA 11.2kW UPS Spare/Replacement Power Module - for SU16000RT4U or SU16000RT4UHW

MODEL NUMBER: **SU16000RT4UPM**



Highlights

- 16,000VA on-line 4U replacement power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving SU16000RT4U or SU16000RT4UHW

Package Includes

- SU16000RT4UPM POWER MODULE ONLY (4U)

Description

16,000 VA (16kVA) on-line, double-conversion UPS replacement power module for UPS configurations involving SU16000RT4U or SU16000RT4UHW

Features

- 16,000VA on-line 4U replacement power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving SU16000RT4U or SU16000RT4UHW
- REPLACEMENT POWER MODULE ONLY

Specifications

OVERVIEW	
UPC Code	037332136565
OUTPUT	
Output Volt Amp Capacity (VA)	16000
Output kVA Capacity (kVA)	12
Output Watt Capacity (Watts)	11200
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (AC Mode)	Sine wave



Output AC Waveform (Battery Mode)	Pure Sine wave
PHYSICAL	
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	706
Primary UPS Height (mm)	178
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / cm)	33.02 x 58.42 x 83.82
Shipping Dimensions (hwd / in.)	13.00 x 23.00 x 33.00
Shipping Weight (kg)	56.70
Shipping Weight (lbs.)	125.00
Unit Dimension Details	4U power module component only.
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	17.78 x 44.45 x 70.61
UPS Power Module Dimensions (hwd, in.)	7 x 17.5 x 27.8
UPS Power Module Weight (kg)	39.01
UPS Power Module Weight (lbs.)	86
COMMUNICATIONS	
Communications Interface	Contact closure; DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface
STANDARDS & COMPLIANCE	
UPS Certifications	Meets FCC Part 15 Category A (EMI); ROHS (Restriction of Hazardous Substances); Tested to CSA (Canada); Tested to UL1778 (USA)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>