

## 3 Breaker Maintenance Bypass Panel for select Tripp Lite 20 and 30kVA UPS systems

MODEL NUMBER: **SU2030KMBP**



### Highlights

- Wallmount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Mechanical interlock system enhances system reliability
- Minimizes sequencing errors
- 3 built-in CH Type circuit breakers
- Compatible with select Tripp Lite 20 and 30kVA 3 phase UPS systems

### Description

Wallmount 3 breaker manual bypass panel with mechanical interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 100A breaker with KAIC rating of 10. Compatible with Tripp Lite SU20K3/3, SU20K3/3XR5, SU30K3/3 and SU30K3/3XR5.

### Features

- Wallmount 3 breaker manual bypass panel with mechanical interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 100A breaker with KAIC rating of 10
- Compatible with Tripp Lite SU20K3/3, SU20K3/3XR5, SU30K3/3, SU30K3/3XR5 and SV20K\_\_ models.

## Specifications

| OVERVIEW                          |                                      |
|-----------------------------------|--------------------------------------|
| UPC Code                          | 037332181800                         |
| INPUT                             |                                      |
| Nominal Input Voltage Description | 208Y/120 VAC 3 phase, 4 wire, Ground |
| OUTPUT                            |                                      |
| Output Capacity Details           | 100A maximum per phase               |
| PHYSICAL                          |                                      |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Form Factors Supported              | Wallmount               |
| Shipping Dimensions (hwd / cm)      | 19.05 x 36.83 x 67.31   |
| Shipping Dimensions (hwd / in.)     | 7.50 x 14.50 x 26.50    |
| Shipping Weight (kg)                | 15.20                   |
| Shipping Weight (lbs.)              | 33.50                   |
| Unit Dimensions (hwd / cm)          | 30.5 x 61 x 11.7        |
| Unit Dimensions (hwd / in.)         | 12 x 24 x 4.6           |
| Unit Weight (kg)                    | 12.47                   |
| Unit Weight (lbs.)                  | 27.5                    |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 1-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>