

## 3 Breaker Maintenance Bypass Panel for 40kVA SV40K and SU40K UPS models

MODEL NUMBER: **SU40KMBPK**



### Highlights

- Wallmount manual bypass panel isolates UPS from connected loads for maintenance with no loss of network availability
- Includes Kirk-Key interlock system enhances system reliability
- 3 built-in circuit breakers, heavy duty buswork
- Compatible with select Tripp Lite 3 phase UPS systems

### Description

Wallmount 3 breaker manual bypass panel with Kirk Key interlock system isolates the UPS from connected loads for maintenance with no loss of network availability. 150A breaker with KAIC rating of 65. Key included.

Compatible with Tripp Lite SU40K

### Features

- Wallmount 3 breaker manual bypass panel with Kirk Key interlock system
- Isolates the UPS from connected loads for maintenance with no loss of network availability
- 150A breaker with KAIC rating of 65
- Key included
- Compatible with Tripp Lite SU40K, and SV40K\_\_ models.

## Specifications

| OVERVIEW                           |              |
|------------------------------------|--------------|
| UPC Code                           | 037332146274 |
| INPUT                              |              |
| Nominal Input Voltage(s) Supported | 240V AC      |
| Voltage Compatibility (VAC)        | 240          |
| PHYSICAL                           |              |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                         |
|-------------------------------------|-------------------------|
| Form Factors Supported              | Wallmount               |
| Shipping Dimensions (hwd / cm)      | 76.20 x 33.02 x 109.22  |
| Shipping Dimensions (hwd / in.)     | 30.00 x 13.00 x 43.00   |
| Shipping Weight (kg)                | 102.06                  |
| Shipping Weight (lbs.)              | 225.00                  |
| Unit Dimensions (hwd / cm)          | 107.6 x 76.5 x 29.8     |
| Unit Dimensions (hwd / in.)         | 42.36 x 30.12 x 11.75   |
| Unit Weight (kg)                    | 99.79                   |
| Unit Weight (lbs.)                  | 220                     |
| <b>WARRANTY</b>                     |                         |
| Product Warranty Period (Worldwide) | 2-year limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>