

## SmartOnline 6000VA Power Module - Hot-swappable replacement power module

MODEL NUMBER: **SU6000RT4UHVPM**



### Highlights

- 6000VA on-line 4U rack/tower hot-swappable replacement power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving several 6kVA UPS configurations

### Package Includes

- SU6000RT4UHVPM power module with internal batteries
- 4POSTRAILKIT mounting kit
- USB, Serial and EPO cabling
- PowerAlert Software

### Description

6,000 VA (6kVA) on-line, double-conversion UPS power module for spare or redundant UPS configurations involving SU6000RT4UHV, SU6000RT4UHVVG, SU6000RT4UHVHW, SU6000RT4UTF, SU6000RT4UTFHW and SU12KRT4UHW product bundles. POWER MODULE ONLY.

## Specifications

OVERVIEW	
UPC Code	037332151803
Accessory Type	Power Module
Accessory Class	UPS Accessories
OUTPUT	
Output Capacity (VA)	6000
Output Capacity (kVA)	6
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
BATTERY	
DC System Voltage (VDC)	192
Battery Access	Front panel battery access door

Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//tripplite.eaton.com/4U-UPS-Replacement-192VDC-Battery-Cartridge-1-set-of-16-Tripp-Lite-SmartOnline-UPS~RBC5-192">RBC5-192</a>&nbsp;</td>
Battery Replacement Description	Hot-swappable, user replaceable internal batteries
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
<b>PHYSICAL</b>	
Primary Form Factor	Rackmount
Minimum Required Rack Depth (cm)	60.96
Minimum Required Rack Depth (inches)	24
Primary UPS Depth (mm)	525
Primary UPS Height (mm)	174
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / in.)	12.00 x 23.50 x 28.50
Shipping Dimensions (hwd / cm)	30.48 x 59.69 x 72.39
Shipping Weight (lbs.)	154.00
Shipping Weight (kg)	69.85
Unit Dimension Details	4U replacement power module component only
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	17.40 x 44.45 x 52.50
UPS Power Module Dimensions (hwd, in.)	6.85 x 17.5 x 20.67
UPS Power Module Weight (kg)	48.99
UPS Power Module Weight (lbs.)	108
Unit Dimensions (hwd / in.)	6.850 x 17.500 x 20.670
<b>FEATURES &amp; SPECIFICATIONS</b>	
IP68 Rated	No
IP20 Rated	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CSA (Canada); IEC/EN 62040; NOM (Mexico); UL 1778

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Product Compliance	RoHS; FCC Part 15 Class A (USA); UKCA
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.