

SmartOnline 6000VA Power Module - Hot-swappable replacement power module

MODEL NUMBER: **SU6000RT4UHVPM**



Highlights

- 6000VA on-line 4U rack/tower hot-swappable replacement power module
- Ideal for use as a spare or replacement power module for mission-critical UPS configurations involving several 6kVA UPS configurations

Package Includes

- SU6000RT4UHVPM power module with internal batteries
- 4POSTRAILKIT mounting kit
- USB, Serial and EPO cabling
- PowerAlert Software

Description

6,000 VA (6kVA) on-line, double-conversion UPS power module for spare or redundant UPS configurations involving SU6000RT4UHV, SU6000RT4UHVVG, SU6000RT4UHVHW, SU6000RT4UTF, SU6000RT4UTFHW and SU12KRT4UHW product bundles. POWER MODULE ONLY.

Specifications

OVERVIEW	
UPC Code	037332151803
OUTPUT	
Output Volt Amp Capacity (VA)	6000
Output kVA Capacity (kVA)	6
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
BATTERY	
DC System Voltage (VDC)	192
Internal UPS Replacement Battery Cartridge	 RBC5-192
Battery Access	Front panel battery access door
Battery Replacement Description	Hot-swappable, user replaceable internal batteries



USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
PHYSICAL	
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	525
Primary UPS Height (mm)	174
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / cm)	30.48 x 59.69 x 72.39
Shipping Dimensions (hwd / in.)	12.00 x 23.50 x 28.50
Shipping Weight (kg)	69.85
Shipping Weight (lbs.)	154.00
Unit Dimension Details	4U replacement power module component only
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	17.40 x 44.45 x 52.50
UPS Power Module Dimensions (hwd, in.)	6.85 x 17.5 x 20.67
UPS Power Module Weight (kg)	48.99
UPS Power Module Weight (lbs.)	108
STANDARDS & COMPLIANCE	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
Certification Details	IEC61000-4-5 1995 B Surge Immunity, EN62040-2
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>