

SmartOnline 200-240V 8kVA 7.2kW Hot-Swap Spare Power Module - for redundant power applications

MODEL NUMBER: **SU8000RT3UPM**



Highlights

- 8000VA on-line 3U rack/tower hot-swappable power module
- Ideal for use as a spare or redundant power module for mission-critical UPS configurations involving SU8000RT3UPM

Package Includes

- SU8000RT3UPM POWER MODULE ONLY (3u)

Description

8,000 VA (8kVA) on-line, double-conversion UPS power module for spare or redundant UPS configurations involving SU8000RT3U or SU8000RT3U1TF UPS bundles. POWER MODULE ONLY.

Features

- 8,000VA (8kVA) on-line, double-conversion UPS power module for spare or redundant UPS configurations involving SU8000RT3U or SU8000RT3U1TF UPS bundles.
- POWER MODULE ONLY

Specifications

OVERVIEW	
UPC Code	037332136503
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC
OUTPUT	
Output Volt Amp Capacity (VA)	8000
Output kVA Capacity (kVA)	8
Output Watt Capacity (Watts)	7200
Output kW Capacity (kW)	7.2



Power Factor	0.9
Crest Factor	3:1
Frequency Compatibility	50 / 60 Hz
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	Pure Sine wave
Nominal Output Voltage(s) Supported	200V; 208V; 220V; 230V; 240V
BATTERY	
DC System Voltage (VDC)	240
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Selectable LCD display with scroll and selection buttons enables UPS control and detailed monitoring options; LED/LCD panel rotates for viewing in rack/tower formats (see manual)
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; 2 additional switches support set and execute scrolling LCD functions
Alarm Cancel Operation	Alarm cancel switch
Audible Alarm	Unique audible alarms for all major UPS, environmental and power conditions (see manual)
PHYSICAL	
Primary Form Factor	Rackmount
Primary UPS Depth (mm)	656
Primary UPS Height (mm)	131
Primary UPS Width (mm)	445
Shipping Dimensions (hwd / cm)	23.62 x 58.93 x 99.06
Shipping Dimensions (hwd / in.)	9.30 x 23.20 x 39.00
Shipping Weight (kg)	30.39
Shipping Weight (lbs.)	67.00
Unit Dimension Details	3U power module component only
UPS Housing Material	Steel
UPS Power Module Dimensions (hwd, cm)	13.06 x 44.45 x 65.58
UPS Power Module Dimensions (hwd, in.)	5.14 x 17.5 x 25.82
UPS Power Module Weight (kg)	19.50
UPS Power Module Weight (lbs.)	43
COMMUNICATIONS	
Communications Interface	USB (HID enabled); DB9 Serial; EPO (emergency power off); Slot for SNMP/Web interface



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

STANDARDS & COMPLIANCE	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category A (EMI)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>