

SUPDM710HW - UPS Accessory - Hardwire PDU Module

MODEL NUMBER: **SUPDM710HW**



Highlights

- Converts compatible SmartOnline high-voltage UPS systems to a totally hardwired solution
- For use with SU10000RT3U and SU8000RT3U UPS Systems
- Hardwired input/output connections
- Easy quick-connect terminal block installation

System Requirements

- Use with SU10000RT3U and SU8000RT3U SmartOnline UPS Systems

Package Includes

- Hardwire PDU
- Mounting Hardware
- Owner's Manual

Description

The SUPDM710HW converts the output of SmartOnline® SU8000RT3U and SU10000RT3U to a totally hardwired solution. Easy quick-connect terminal blocks allow installation in minutes. Can accept input voltages of 200-240 VAC. Hardwire input/output connections.

Features

- Converts the output of SmartOnline SU8000RT3U and SU10000RT3U to a totally hardwired solution
- Easy quick-connect terminal blocks allow installation in minutes
- Can accept input voltages of 200-240 VAC
- Hardwire input/output connections

Specifications

OVERVIEW	
UPC Code	037332127167
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	208V AC; 240V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	208; 240
OUTPUT	
Frequency Compatibility	50 / 60 Hz



Powering Business Worldwide



Output Receptacles	Hardwire
Output Nominal Voltage	200-240v
PHYSICAL	
Material of Construction	Steel
Shipping Dimensions (hwd / in.)	8.30 x 9.30 x 12.80
Shipping Dimensions (hwd / cm)	21.08 x 23.62 x 32.51
Shipping Weight (lbs.)	6.80
Shipping Weight (kg)	3.08
Unit Dimensions (hwd / in.)	5.250 x 7.500 x 5.250
Unit Dimensions (hwd / cm)	13.3 x 19.1 x 13.3
Unit Weight (lbs.)	3.8
Unit Weight (kg)	1.72
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.