

Detachable redundant PDU option for select SmartOnline UPS - Hardwired input / output

MODEL NUMBER: SUPDMB20KHW



Description

SUPDMB20KHW combines the output of two compatible SU8000RT3UPM or SU10000RT3UPM UPS power modules for fault-tolerant N+1 or increased capacity configurations. Manual bypass feature enables hot-swappable replacement of both power modules with no disruption in power to connected equipment. (IMPORTANT > compatible only with SU8000RT3UPM and SU10000RT3UPM power modules built after 6/2010 with built-in USB and PARALLEL back panel data connections).

Features

<p> </p>

Highlights

- Converts compatible SmartOnline 8 and 10kVA high-voltage UPS configurations for N+1 redundancy or increased capacity when used along with a 2nd compatible UPS power module
- Manual bypass feature enables hot-swappable replacement of both power modules while connected equipment runs uninterrupted
- Hardwired input and output connections

System Requirements

- For use only with configurations involving two compatible SU8000RT3UPM or SU10000RT3UPM power modules (requires two of the same model power module built after 6/2010 originally shipping with built-in USB and PARALLEL back panel data connections)

Package Includes

- SUPDMB20KHW parallel PDU
- Parallel cable
- Owner's Manual

Specifications

OVERVIEW	
UPC Code	037332153982
INPUT	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 230; 240; 220
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	Hardwire
Output Nominal Voltage	200-240VAC
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / cm)	28.19 x 33.02 x 59.44
Shipping Dimensions (hwd / in.)	11.10 x 13.00 x 23.40
Shipping Weight (kg)	7.71
Shipping Weight (lbs.)	17.00
Unit Dimensions (hwd / cm)	52.1 x 17.8 x 11.4
Unit Dimensions (hwd / in.)	20.5 x 7 x 4.5
Unit Weight (kg)	6.59
Unit Weight (lbs.)	14.52
STANDARDS & COMPLIANCE	
Certifications	Tested to UL1778 4th Edition (USA), CSA (Canada), CE, EN62040-1
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>