

Detachable PDU option for compatible SmartOnline UPS Systems, L6-30P/L6-20R and L6-30R

MODEL NUMBER: **SUPDMB6K**



Description

The SUPDMB6K UPS backplate with manual transfer switch serves as a replacement for the original backplate provided with SU6000RT4UHV and SU6000RT4UTF configurations. Can also be used to convert any UPS configuration using the SU6000RT4UHVPM power module to support hardwire input with L6-20R and L6-30R output receptacles. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input / 2 L6-30R and 2 L6-20R outlets.

Features

Highlights

- Detachable PDU backplate with manual bypass switch serves as a replacement PDU for configured SU6000RT4UHV and SU6000RT4UTF UPS systems
- Can also be used to convert any UPS configuration using the SU6000RT4UHVPM power module to include L6-20R and L6-30R outlets
- 2 L6-20R and 2 L6-30R outlets
- L6-30P input supported
- Attaches via unit-specific back panel electrical and bolt-on connections
- Manual bypass feature ensures maximum equipment availability

System Requirements

- Requires SU6000RT4UHVPM UPS Power Module

Package Includes

- SUPDMB6K detachable PDU

Specifications

OVERVIEW	
UPC Code	037332153920
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	L6-30P (10ft / 3m)
Voltage Compatibility (VAC)	200; 208; 220; 230; 240
OUTPUT	
Frequency Compatibility	50 / 60 Hz



Powering Business Worldwide



Output Receptacles	(2) L6-20R; (2) L6-30R
Output Nominal Voltage	200, 208, 220, 230, 240 VAC
Overload Protection	1 double pole 20A breaker protects both L6-20R outlets
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / in.)	10.30 x 6.70 x 19.50
Shipping Dimensions (hwd / cm)	26.16 x 17.02 x 49.53
Shipping Weight (lbs.)	9.70
Shipping Weight (kg)	4.40
Unit Dimensions (hwd / in.)	3.310 x 17.210 x 3.190
Unit Dimensions (hwd / cm)	8.4 x 43.7 x 8.1
Unit Weight (lbs.)	8.2
Unit Weight (kg)	3.72
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.