

Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/Output

MODEL NUMBER: **SUPDMB6KHW**



Description

The SUPDMB6KHW UPS backplate with manual transfer switch serves as a replacement for the original backplate provided with SU6000RT4UHVHW and SU6000RT4UTFHW configurations. Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to support hardwire input and output. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input and output.

Features

Highlights

- Detachable PDU backplate with manual bypass switch serves as a replacement PDU for configured SU6000RT4UHVHW and SU6000RT4UTFHW UPS systems
- Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to include hardwire output
- Hardwire input and output supported
- Attaches via unit-specific back panel electrical and bolt-on connections
- Manual bypass feature ensures maximum equipment availability

System Requirements

- Requires SU6000RT4UHVPM UPS power module in any 200-240V AC configuration

Package Includes

- SUPDMB6KHW detachable PDU

Specifications

OVERVIEW	
UPC Code	037332153739
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	Hardwire
Output Nominal Voltage	200, 208, 220, 230, 240 VAC
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / cm)	26.16 x 16.51 x 49.28
Shipping Dimensions (hwd / in.)	10.30 x 6.50 x 19.40
Shipping Weight (kg)	3.36
Shipping Weight (lbs.)	7.40
Unit Dimensions (hwd / cm)	8.4 x 43.7 x 8.1
Unit Dimensions (hwd / in.)	3.3 x 17.2 x 3.2
Unit Weight (kg)	3.49
Unit Weight (lbs.)	7.7
STANDARDS & COMPLIANCE	
Certifications	Tested to UL1778 (USA), CSA (Canada), CE (EU)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>