

Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/C19 Outlets

MODEL NUMBER: SUPDMB6KIEC



Description

The SUPDMB6KIEC UPS backplate with manual transfer switch serves as a replacement for the original backplate provided with SU6000RT4UHVG configurations. Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to support hardwire input and 4 C19 output receptacles. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input / 4 C19 output connections.

Features

Highlights

- Detachable PDU backplate with manual bypass switch serves as a replacement PDU for configured SU6000RT4UHVG UPS systems
- Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to include C19 outlets
- 4 C19 output receptacles
- Hardwire input supported
- Attaches via unit-specific back panel electrical and bolt-on connections
- Manual bypass feature ensures maximum equipment availability

System Requirements

- Requires SU6000RT4UHVPM UPS power module in any 200-240V AC configuration

Package Includes

- SUPDMB6KIEC detachable PDU

Specifications

OVERVIEW	
UPC Code	037332153746
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240
OUTPUT	
Frequency Compatibility	50 / 60 Hz



Powering Business Worldwide



Output Receptacles	(2) C19
Output Nominal Voltage	200, 208, 220, 230, 240 VAC
Overload Protection	2 double pole 20A breakers protect 2 C19 outlets each
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / in.)	6.89 x 20.08 x 10.79
Shipping Dimensions (hwd / cm)	17.50 x 51.00 x 27.41
Shipping Weight (lbs.)	7.70
Shipping Weight (kg)	3.49
Unit Dimensions (hwd / in.)	3.300 x 17.200 x 3.190
Unit Dimensions (hwd / cm)	8.4 x 43.7 x 8.1
Unit Weight (lbs.)	7.7
Unit Weight (kg)	3.49
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.