

## Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/C19 Outlets

MODEL NUMBER: SUPDMB6KIEC



### Description

The SUPDMB6KIEC UPS backplate with manual transfer switch serves as a replacement for the original backplate provided with SU6000RT4UHVG configurations. Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to support hardwire input and 4 C19 output receptacles. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input / 4 C19 output connections.

### Features

## Specifications

OVERVIEW	
UPC Code	037332153746
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240
OUTPUT	

### Highlights

- Detachable PDU backplate with manual bypass switch serves as a replacement PDU for configured SU6000RT4UHVG UPS systems
- Can also be used to convert any high voltage UPS configuration using the SU6000RT4UHVPM power module to include C19 outlets
- 4 C19 output receptacles
- Hardwire input supported
- Attaches via unit-specific back panel electrical and bolt-on connections
- Manual bypass feature ensures maximum equipment availability

### System Requirements

- Requires SU6000RT4UHVPM UPS power module in any 200-240V AC configuration

### Package Includes

- SUPDMB6KIEC detachable PDU



Frequency Compatibility	50 / 60 Hz
Output Receptacles	(2) C19
Output Nominal Voltage	200, 208, 220, 230, 240 VAC
Overload Protection	2 double pole 20A breakers protect 2 C19 outlets each
<b>PHYSICAL</b>	
Material of Construction	Metal
Shipping Dimensions (hwd / cm)	17.50 x 51.00 x 27.41
Shipping Dimensions (hwd / in.)	6.89 x 20.08 x 10.79
Shipping Weight (kg)	3.49
Shipping Weight (lbs.)	7.70
Unit Dimensions (hwd / in.)	3.3 x 17.2 x 3.2
Unit Dimensions (hwd / cm)	8.4 x 43.7 x 8.1
Unit Weight (lbs.)	7.7
Unit Weight (kg)	3.49
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL1778 (USA), CSA (Canada), CE (EU)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>