

Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/L6-20R and L6-30R

MODEL NUMBER: SUPDMB710



Description

The SUPDMB710 converts the output of SmartOnline SU8000RT3U and SU10000RT3U power modules to North American L6-20R and L6-30R output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input / 2 L6-30R and 4 L6-20R output connections.

Features

- Converts compatible SmartOnline high-voltage UPS systems to provide North American 20 and 30A outputs
- For use with input voltages of 200-240 VAC
- Hardwired input / 2 L6-30R and 4 L6-20R output connections
- Manual bypass feature ensures maximum equipment availability

Specifications

OVERVIEW	
UPC Code	037332126672
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240

Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide North American 20 and 30A outputs
- For use with input voltages of 200-240 VAC
- Hardwired input / 2 L6-30R and 4 L6-20R output connections
- Manual bypass feature ensures maximum equipment availability

System Requirements

- For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

Package Includes

- SUPDMB710 detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions



OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) L6-20R; (2) L6-30R
Output Nominal Voltage	208/240 VAC
Overload Protection	2 double pole 30A breakers, 2 double pole 20A breakers
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / cm)	34.04 x 23.88 x 23.88
Shipping Dimensions (hwd / in.)	13.40 x 9.40 x 9.40
Shipping Weight (kg)	4.90
Shipping Weight (lbs.)	10.80
Unit Dimensions (hwd / in.)	10.25 x 7.5 x 6.5
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5
Unit Weight (lbs.)	8.75
Unit Weight (kg)	3.97
STANDARDS & COMPLIANCE	
Certifications	Tested to UL1778 (USA), CSA (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>