

## Detachable PDU option for compatible SmartOnline UPS Systems, Hardwired Input/L6-20R and L6-30R

MODEL NUMBER: SUPDMB710



### Description

The SUPDMB710 converts the output of SmartOnline SU8000RT3U and SU10000RT3U power modules to North American L6-20R and L6-30R output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input / 2 L6-30R and 4 L6-20R output connections.

### Features

- Converts compatible SmartOnline high-voltage UPS systems to provide North American 20 and 30A outputs
- For use with input voltages of 200-240 VAC
- Hardwired input / 2 L6-30R and 4 L6-20R output connections
- Manual bypass feature ensures maximum equipment availability

## Specifications

OVERVIEW	
UPC Code	037332126672
Accessory Type	PDU Module
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire
Voltage Compatibility (VAC)	200; 208; 220; 230; 240

### Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide North American 20 and 30A outputs
- For use with input voltages of 200-240 VAC
- Hardwired input / 2 L6-30R and 4 L6-20R output connections
- Manual bypass feature ensures maximum equipment availability

### System Requirements

- For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

### Package Includes

- SUPDMB710 detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions

OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(4) L6-20R; (2) L6-30R
Output Nominal Voltage	208/240 VAC
Overload Protection	2 double pole 30A breakers, 2 double pole 20A breakers
PHYSICAL	
Material of Construction	Metal
Shipping Dimensions (hwd / in.)	13.40 x 9.40 x 9.40
Shipping Dimensions (hwd / cm)	34.04 x 23.88 x 23.88
Shipping Weight (lbs.)	10.80
Shipping Weight (kg)	4.90
Unit Dimensions (hwd / in.)	10.250 x 7.500 x 6.500
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5
Unit Weight (lbs.)	8.75
Unit Weight (kg)	3.97
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); UL 1778
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty