

UPS Maintenance Bypass Panel for SUT30K - 3 Breakers

MODEL NUMBER: **SUT30KMBP**



This bypass panel isolates an SUT30K 3-Phase UPS system from connected loads during maintenance.

Features

Bypass an SUT30K UPS to Perform Maintenance For use with the SUT30K 3-phase UPS system, the SUT30KMBP maintenance bypass panel (MBP) maintains total continuity of power to connected load circuits when bypass of the UPS is required for regular service and maintenance. This UPS maintenance bypass panel has three 4-pole circuit breakers for Input, Bypass and Output. The breakers have removable handles to allow the panel's trim cover to be removed for internal access. The short circuit rating is 10 kAIC. Maximum current capacity is 125A.

Convenient Wall-Mount Installation Made of galvanized steel, the service bypass panel has rear mounting holes for installation on a smooth and solid wall (mounting hardware not included).

One-Year Warranty The SUT30KMBP is backed by a one-year limited warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	037332222350
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage Description	208Y/120 VAC 3 phase, 4 wire (3P+N+E)
OUTPUT	
Output Capacity Details	125A maximum

Highlights

- Isolates a SUT30K UPS from connected loads to permit maintenance
- Allows connected loads to remain continuously powered
- Three built-in 4-pole circuit breakers for Input, Bypass and Output
- Mounting holes for convenient wall installation
- Maximum current capacity is 125A

Applications

- Bypass an SUT30K UPS system to perform maintenance

Package Includes

- SUT30KMBP UPS Maintenance Bypass Panel for SUT30K
- Installation and Operation Manual



Powering Business Worldwide



PHYSICAL	
Form Factors Supported	Wallmount
Shipping Dimensions (hwd / in.)	10.00 x 22.00 x 25.00
Shipping Weight (kg)	17.24
Unit Dimensions (hwd / in.)	17.500 x 20.000 x 4.600
Unit Dimensions (hwd / cm)	44.45 x 50.8 x 11.68
Unit Weight (lbs.)	28
Unit Weight (kg)	12.70
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.