

# UPS Maintenance Bypass Panel for SUT40K - 3 Breakers

MODEL NUMBER: **SUT40KMBP**



This bypass panel isolates an SUT40K 3-Phase UPS system from connected loads during maintenance.

## Features

**Bypass an SUT40K UPS to Perform Maintenance** For use with the SUT40K 3-phase UPS system, the SUT40KMBP maintenance bypass panel (MBP) maintains total continuity of power to connected load circuits when bypass of the UPS is required for regular service and maintenance. This UPS maintenance bypass panel has three 4-pole circuit breakers for Input, Bypass and Output. The breakers have removable handles to allow the panel's trim cover to be removed for internal access. Maximum current capacity is 150A.

**Convenient Wall-Mount Installation** Made of galvanized steel, the service bypass panel has rear mounting holes for installation on a smooth and solid wall (mounting hardware not included).

**One-Year Warranty** The SUT40KMBP is backed by a one-year limited warranty, ensuring reliability and performance.

## Specifications

OVERVIEW	
UPC Code	037332222367
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage Description	208Y/120 VAC 3 phase, 4 wire (3P+N+E)
OUTPUT	
Output Capacity Details	150A maximum

## Highlights

- Isolates a SUT40K UPS from connected loads to permit maintenance
- Allows connected loads to remain continuously powered
- Three built-in 4-pole circuit breakers for Input, Bypass and Output
- Mounting holes for convenient wall installation
- Maximum current capacity is 150A

## Applications

- Bypass an SUT40K UPS system to perform maintenance

## Package Includes

- SUT40KMBP UPS Maintenance Bypass Panel for SUT40K
- Installation and Operation Manual



Powering Business Worldwide



PHYSICAL	
Form Factors Supported	Wallmount
Shipping Dimensions (hwd / in.)	13.50 x 42.00 x 36.00
Shipping Weight (kg)	56.25
Unit Dimensions (hwd / in.)	28.130 x 31.500 x 6.980
Unit Dimensions (hwd / cm)	71.45 x 80.01 x 17.73
Unit Weight (lbs.)	124
Unit Weight (kg)	56.25
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.