

UPS Maintenance Bypass Panel for SUT60K - 3 Breakers

MODEL NUMBER: **SUT60KMBP**



This bypass panel isolates an SUT60K 3-Phase UPS system from connected loads during maintenance.

Features

Bypass an SUT60K UPS to Perform Maintenance For use with Tripp Lite's SUT60K 3-phase UPS system, the SUT60KMBP maintenance bypass panel (MBP) maintains total continuity of power to connected load circuits when bypass of the UPS is required for regular service and maintenance. This UPS maintenance bypass panel has three 4-pole circuit breakers for Input, Bypass and Output. The breakers have removable handles to allow the panel's trim cover to be removed for internal access. Maximum current capacity is 225A.

Convenient Wall-Mount Installation Made of galvanized steel, the service bypass panel has rear mounting holes for installation on a smooth and solid wall (mounting hardware not included).

One-Year Warranty The SUT60KMBP is backed by a one-year limited warranty, ensuring reliability and performance.

Highlights

- Isolates a Tripp Lite SUT60K UPS from connected loads to permit maintenance
- Allows connected loads to remain continuously powered
- Three built-in 4-pole circuit breakers for Input, Bypass and Output
- Mounting holes for convenient wall installation
- Maximum current capacity is 225A

Applications

- Bypass an SUT60K UPS system to perform maintenance

Package Includes

- SUT60KMBP UPS Maintenance Bypass Panel for SUT60K
- Installation and Operation Manual

Specifications

OVERVIEW	
UPC Code	03733222374
INPUT	
Nominal Input Voltage Description	208Y/120 VAC 3 phase, 4 wire (3P+N+E)
OUTPUT	
Output Capacity Details	225A maximum
PHYSICAL	
Form Factors Supported	Wallmount
Unit Dimensions (hwd / cm)	80 x 97.8 x 150



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Dimensions (hwd / in.)	31.5 x 38.5 x 5.89
Unit Weight (kg)	38.56
Unit Weight (lbs.)	85
STANDARDS & COMPLIANCE	
Certifications	Tested to UL (USA), cUL (Canada), NOM (Mexico)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>