

UPS Maintenance Bypass Panel for SUT60K - 3 Breakers

MODEL NUMBER: **SUT60KMBP**



This bypass panel isolates an SUT60K 3-Phase UPS system from connected loads during maintenance.

Features

Bypass an SUT60K UPS to Perform Maintenance For use with the SUT60K 3-phase UPS system, the SUT60KMBP maintenance bypass panel (MBP) maintains total continuity of power to connected load circuits when bypass of the UPS is required for regular service and maintenance. This UPS maintenance bypass panel has three 4-pole circuit breakers for Input, Bypass and Output. The breakers have removable handles to allow the panel's trim cover to be removed for internal access. Maximum current capacity is 225A.

Convenient Wall-Mount Installation Made of galvanized steel, the service bypass panel has rear mounting holes for installation on a smooth and solid wall (mounting hardware not included).

One-Year Warranty The SUT60KMBP is backed by a one-year limited warranty, ensuring reliability and performance.

Specifications

OVERVIEW	
UPC Code	03733222374
Accessory Type	Bypass Panel
Accessory Class	UPS Accessories
INPUT	
Nominal Input Voltage Description	208Y/120 VAC 3 phase, 4 wire (3P+N+E)
OUTPUT	
Output Capacity Details	225A maximum

Highlights

- Isolates a SUT60K UPS from connected loads to permit maintenance
- Allows connected loads to remain continuously powered
- Three built-in 4-pole circuit breakers for Input, Bypass and Output
- Mounting holes for convenient wall installation
- Maximum current capacity is 225A

Applications

- Bypass an SUT60K UPS system to perform maintenance

Package Includes

- SUT60KMBP UPS Maintenance Bypass Panel for SUT60K
- Installation and Operation Manual



Powering Business Worldwide



PHYSICAL	
Form Factors Supported	Wallmount
Shipping Weight (kg)	38.56
Unit Dimensions (hwd / in.)	31.500 x 38.500 x 5.890
Unit Dimensions (hwd / cm)	80 x 97.8 x 150
Unit Weight (lbs.)	85
Unit Weight (kg)	38.56
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico); UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.