

5kVA 120V Stepdown Transformer - 18 NEMA 5-20R Outlets, 60 Hz, L6-30P Input, 3 ft. Cord, 3U Rack/Tower

MODEL NUMBER: **SUTFMR**



5kVA transformer converts UPS 208V input to 120V for powering low-voltage AC components.

Features

208V to 120V Isolation Transformer Converts High-Voltage Input to Low-Voltage Output

This 5kVA Stepdown Transformer converts your UPS system's 208V high-voltage input to 120V low-voltage output. It features 18 NEMA 5-20R outlets (two sets of nine outlets) for connecting equipment with common NEMA 5-15P and NEMA 5-20P plugs. Resettable 20A circuit breakers protect your 120V equipment against overload conditions. The SUTFMR works with select 5kVA to 6kVA SmartOnline® UPS systems.

Versatile Installation Options

You can mount the SUTFMR in 3U of space in an EIA-standard 19-inch rack using the included 4-post rail kit or an optional 2-post rail kit (RK2PC, sold separately). You can also adapt it for tower installation using the included joining bracket and hardware. The three-foot power cord with L6-30P plug connects to a compatible AC outlet.

Specifications

OVERVIEW	
UPC Code	786689811747
UPS Type	On-Line
Accessory Type	Isolation Transformer
Accessory Class	UPS Accessories
INPUT	
Input Phase	Single-Phase
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 220V AC; 230V AC; 240V AC

Highlights

- Converts 208V AC input into 120V output for powering low-voltage equipment
- 18 NEMA 5-20R 120V outlets for connecting components with 5-15P or 5-20P plugs
- Resettable circuit breakers protect mission-critical equipment from hazardous overloads
- 3 ft. power cord with L6-30P input plug connects to compatible AC source

System Requirements

Compatible with SU5000RT, SU5000RTMB, SU5000RTF, SU5000RTFMB, SU6000RT, SU6000RTMB, SU6000RTF and SU6000RTFMB UPS systems

Package Includes

- SUTFMR 5kVA 120V Stepdown Transformer
- Joining bracket and hardware for tower configuration
- Rack-mounting hardware
- Owner's manuals



Powering Business Worldwide

TRIPP LITE
SERIES

UPS Input Connection Type	L6-30P
UPS Input Cord Length (ft.)	3
UPS Input Cord Length (m)	0.9
Input Connection Type	L6-30P
Plug Type	L6-30P
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(18) 5-20R
Output Nominal Voltage	120V
Individually Controllable Load Banks	No
BATTERY	
Expandable Runtime	No
PHYSICAL	
Primary Form Factor	Rackmount; Tower
Material of Construction	Metal
Rack Height	3U
Unit Dimensions (hwd / in.)	5.100 x 17.300 x 25.400
Unit Weight (lbs.)	95
Unit Weight (kg)	43.09
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Relative Humidity	0-95% non-condensing
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico)
Product Compliance	CE (Europe); ENERGY STAR Qualified; RoHS
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.