

## 120V Single Phase Whip in 5 ft. (1.52 m) length with L5-20R for Breakered 3-Phase Distribution Cabinets

MODEL NUMBER: **SUWL520C-5**



### Highlights

- 120V single phase whip distribution cabinet accessory
- 5-ft. (1.52 m) length with 3-ft. (0.91 m) removed outer jacket
- 3 conductor 12 AWG stranded wire
- L5-20R outlet (120V 20A)

### Description

120V single phase whip with L5-20R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 5-ft. (1.52 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB120 circuit breaker in SUDC208V series 3 phase distribution racks. L5-20R outlet is compatible with 120V loads and Power Distribution Units (PDUs) supporting a L5-20P plug-in connection.

### Features

- 120V single phase whip with L5-20R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 5-ft. (1.52 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB120 circuit breaker in SUDC208V series 3 phase distribution racks
- L5-20R outlet is compatible with 120V loads and Power Distribution Units (PDUs) supporting a L5-20P plug-in connection

## Specifications

OVERVIEW	
UPC Code	037332156068
INPUT	
Input Connection Type	Hardwire (3 wire - L, N, G)



**Tripp Lite**  
 1111 W. 35th Street  
 Chicago, IL 60609 USA  
 Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (ft.)	5
Cable Length (m)	1.52
<b>OUTPUT</b>	
PDU Recommendation Notes	Compatible with all PDU brands fitted with a L5-20P (20A 120V) input plug, including Tripp Lite <a href="http://www.tripplite.com/2.4kW-Single-Phase-Basic-PDU-120V-Outlets-13-5-15-20R-L5-20P-15ft-Cord-1U-Rack-Mount-PDU1220T">PDU1220T</a> , <a href="http://www.tripplite.com/2.4kW-Single-Phase-Basic-PDU-120V-Outlets-14-5-15-20R-L5-20P-15ft-Cord-0U-Vertical-PDU1420T">PDU1420T</a> , <a href="http://www.tripplite.com/1.6-3.8kW-Single-Phase-Basic-PDU-100-240V-12-C13-2-C19-C20-C14-L6-20P-L5-20P-5-20P-5-15P-1U-PDUNV">PDUNV</a> , <a href="http://www.tripplite.com/1.9kW-Single-Phase-Basic-PDU-120V-Outlets-14-5-15/20R-L5-20P-5-20P-Adapter-15ft-Cord-0U-Vertical-PDUV20">PDUV20</a> , <a href="http://www.tripplite.com/1.92kW-Single-Phase-Metered-PDU-120V-12-5-15-20R-L5-20P-5-20P-110-127V-Input-15ft-Cord-1U-Rack-Mount-PDUMH20">PDUMH20</a> , <a href="http://www.tripplite.com/1.9kW-Single-Phase-Metered-PDU-120V-Outlets-28-5-15-20R-L5-20P-5-20P-Adapter-15ft-Cord-0U-Vertical-PDUMV20">PDUMV20</a> , <a href="http://www.tripplite.com/1.9kW-Single-Phase-Monitored-PDU-120V-Outlets-8-5-15-20R-L5-20P-5-20P-Adapter-12ft-Cord-1U-Rack-Mount-PDUMNH20">PDUMNH20</a> , <a href="http://www.tripplite.com/1.9kW-Single-Phase-Switched-PDU-120V-Outlets-16-5-15-20R-L5-20P-5-20P-input-12ft-Cord-1U-Rack-Mount-TAA-PDUMH20NET">PDUMH20NET</a> and <a href="http://www.tripplite.com/1.9kW-Single-Phase-Switched-PDU-120V-Outlets-16-5-15-20R-L5-20P-5-20P-input-12ft-Cord-1U-Rack-Mount-TAA-PDUMV20NET">PDUMV20NET</a>
Output Receptacles	(1) L5-20R
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	30.48 x 30.48 x 15.24
Shipping Dimensions (hwd / in.)	12.00 x 12.00 x 6.00
Shipping Weight (kg)	2.04
Shipping Weight (lbs.)	4.50
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>