

120V Single Phase Whip in 5 ft. (1.52 m) length with L5-20R for Breakered 3-Phase Distribution Cabinets

MODEL NUMBER: **SUWL520C-5**



Highlights

- 120V single phase whip distribution cabinet accessory
- 5-ft. (1.52 m) length with 3-ft. (0.91 m) removed outer jacket
- 3 conductor 12 AWG stranded wire
- L5-20R outlet (120V 20A)

Description

120V single phase whip with L5-20R outlet distributes power from 3 phase distribution cabinet to critical equipment racks. 5-ft. (1.52 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB120 circuit breaker in SUDC208V series 3 phase distribution racks. L5-20R outlet is compatible with 120V loads and Power Distribution Units (PDUs) supporting a L5-20P plug-in connection.

Features

- 120V single phase whip with L5-20R outlet
- Distributes power from 3 phase distribution cabinet to critical equipment racks
- 5-ft. (1.52 m) insulated and 3-ft. (0.91 m) of removed outer jacket cabling supports hardwire connection to SUBB120 circuit breaker in SUDC208V series 3 phase distribution racks
- L5-20R outlet is compatible with 120V loads and Power Distribution Units (PDUs) supporting a L5-20P plug-in connection

Specifications

OVERVIEW	
UPC Code	037332156068
Accessory Type	Single-Phase Whip Cable
Accessory Class	PDU Accessories
INPUT	
Input Connection Type	Hardwire (3 wire - L, N, G)
OUTPUT	



Powering Business Worldwide

TRIPP LITE
SERIES

PDU Recommendation Notes	Compatible with all PDU brands fitted with a L5-20P (20A 120V) input plug, including Tripp Lite & PDU1220T ; & PDU1420T ; & PDUNV ; & PDUV20 ; & PDUMH20 ; & PDUMV20 ; & PDUMNH20 ; PDUMNV20; & PDUMH20NET ; and PDUMV20NET
Output Receptacles	(1) L5-20R
PHYSICAL	
Color	Black
Cable Length (ft.)	5
Cable Length (m)	1.52
Shipping Dimensions (hwd / in.)	12.00 x 12.00 x 6.00
Shipping Dimensions (hwd / cm)	30.48 x 30.48 x 15.24
Shipping Weight (lbs.)	4.50
Shipping Weight (kg)	2.04
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.