

## Protect It! Surge Protector with 3 Rotatable Outlets, 3 Stationary, side facing Outlets, Direct-Plug In, 1200 Joules

MODEL NUMBER: **SWIVEL6**



### Highlights

- 3 rotatable outlets
- 3 stationary, side facing outlets
- Direct plug-in design
- 1200 joule rating
- Diagnostic LEDs

### Package Includes

- SWIVEL6 Surge Suppressor
- Instruction manual with warranty information

### Description

The SWIVEL6 offers reliable surge and line noise protection. Premium features include a compact, direct plug-in design for easy portability, 3 rotatable outlets and 3 stationary outlets for easier plug connection and removal and 1200 joules of surge absorption protection. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- 3 rotatable outlets and 3 stationary side facing outlets, allow for easier plug connection and removal
- 1200 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332138231
INPUT	



Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	60 Hz
Output (Watts)	1875
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Rotatable, Stationary
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1200
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500, 500, 500
EMI / RFI Filtering	Up to 20 dB
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Material of Construction	Plastic
Power Cord Color	No
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	29mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	6.02 x 4.45 x 20.30
Shipping Dimensions (hwd / cm)	15.29 x 11.30 x 51.56
Shipping Weight (lbs.)	0.74
Shipping Weight (kg)	0.34
Unit Dimensions (hwd / in.)	6.25 x 4 x 2.25
Unit Dimensions (hwd / cm)	15.88 x 10.16 x 5.72
Unit Weight (lbs.)	0.6
Unit Weight (kg)	0.27
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Rotatable Outlets	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Industry Canada (Communications)	Industry Canada
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 42 (Canada); NOM (Mexico); UL 1449; UL 497A; UL 1363
Product Compliance	FCC Part 68; RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 &nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> &nbsp;

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>