

Protect It! Surge Protector with 3 Rotatable Outlets, 3 Stationary, side facing Outlets, Direct-Plug In, 1200 Joules

MODEL NUMBER: **SWIVEL6**



Highlights

- 3 rotatable outlets
- 3 stationary, side facing outlets
- Direct plug-in design
- 1200 joule rating
- Diagnostic LEDs

Package Includes

- SWIVEL6 Surge Suppressor
- Instruction manual with warranty information

Description

The SWIVEL6 offers reliable surge and line noise protection. Premium features include a compact, direct plug-in design for easy portability, 3 rotatable outlets and 3 stationary outlets for easier plug connection and removal and 1200 joules of surge absorption protection. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 3 rotatable outlets and 3 stationary side facing outlets, allow for easier plug connection and removal
- 1200 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- 2 diagnostic LEDs alert user to protection and grounding status
- High-impact plastic housing (black) stands up to the most demanding environments
- Direct plug-in design converts two outlets into six by plugging into any wall outlet
- \$20,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW



| | |
|--|--|
| UPC Code | 037332138231 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Cord Length Details | Direct plug-in |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 0 |
| Right-Angle Plug | No |
| Input Cord Length (m) | 0.00 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 60 Hz |
| Output (Watts) | 1875 |
| Output Receptacles | (6) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | (2) Yes |
| Outlet Orientation | Rotatable, Stationary |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Diagnostic LED(s) | Yes |
| Diagnostic LED Details | Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 1200 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping Voltage (RMS) | 150 |
| UL1449 Let Through Rating | 500, 500, 500 |
| EMI / RFI Filtering | Up to 20 dB |
| Automatic Shut-Off | No |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Antimicrobial Coating | No |
| Color | Black |
| Housing Color | Black |
| Integrated Keyhole Mounting Slots | No |
| Material of Construction | Plastic |
| Outlets Measurement (Center to Center) | 29mm |
| Receptacle Color | Black |
| Shipping Dimensions (hwd / cm) | 15.29 x 11.30 x 51.56 |
| Shipping Dimensions (hwd / in.) | 6.02 x 4.45 x 20.30 |
| Shipping Weight (kg) | 0.34 |
| Shipping Weight (lbs.) | 0.74 |
| Unit Dimensions (hwd / cm) | 15.88 x 10.16 x 5.72 |
| Unit Dimensions (hwd / in.) | 6.25 x 4 x 2.25 |
| Unit Weight (kg) | 0.27 |
| Unit Weight (lbs.) | 0.6 |
| SPECIAL FEATURES | |
| Rotatable Outlets | Yes |
| STANDARDS & COMPLIANCE | |
| Canada | Approved for Canada by ETL |
| Approvals | RoHS |
| UL1449 3rd Edition (AC Suppression) | TESTED TO UL1449 3RD EDITION REQUIREMENTS BY ETL |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$20,000 Ultimate Lifetime Insurance |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>