

Protect It! 6-Outlet Surge Protector with 3 Rotatable Outlets – Direct Plug-In, 1200 Joules, 2 USB Ports

MODEL NUMBER: **SWIVEL6USB**



Swivel surge protector with USB safeguards your home/office electronics against dangerous surges, spikes and line noise.

Features

Swivel Surge Protector with USB Safeguards Your Sensitive Electronics Ideal for your home or office workstation, this Protect It!® 6-outlet swivel surge protector features a surge protection rating of 1200 joules to defend your sensitive electronic components against even strong power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the SWIVEL6USB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

6 Outlets Accept a Wide Range of Electronic Devices The direct plug-in design converts two standard wall outlets into six. Plug your PC, printer, scanner, router, modem, television, stereo receiver and other home/office electronics into six NEMA 5-15R AC outlets to protect them against dangerous surges, spikes and line noise.

2 USB Ports Share 3.1 Amps of Charging Power Dual USB-A ports are available for charging your smartphone, tablets and other USB mobile devices, which are also protected from the damaging effects of surges, spikes and line interference.

Rotating Outlets Help Accommodate Bulky Transformers Three of the six outlets rotate 90 degrees to allow great flexibility in placing connected devices or accepting bulky transformers without blocking adjacent outlets.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This swivel surge protector with USB filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better with longer lifespans.

Includes the Latest Safety Features An integrated 15A circuit breaker protects all outlets and automatically cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and

Highlights

- Rotating outlets accommodate bulky transformers without blocking other outlets
- 1200 joules protect your valuable electronics against dangerous surges/spikes/line noise
- Direct plug-in design (no power cord) for easy transport in briefcase or luggage
- 2 USB ports share 3.1A for fast charging of phone, laptop and other mobile devices

Applications

- Protecting computers, modems, home theater equipment and other valuable electronics against AC power surges and spikes
- Filtering potentially damaging line noise to improve connected equipment's performance and lifespans
- Safeguarding valuable data against damage stemming from unexpected interruptions in power
- Charging a smartphone, tablet or other USB devices via the dual USB ports

Package Includes

- SWIVEL6USB Protect It! 6-Outlet Surge Protector with 3 Rotatable Outlets – Direct Plug-In, 1200 Joules, 2 USB Ports
- Owner's manual



indicating replacement is required. Diagnostic LEDs confirm your wall outlet is properly grounded and your connected equipment is protected. The 6-outlet swivel surge protector conforms to current UL 1449 3rd Edition and cUL (Canada) safety standards. Its high-impact black plastic housing is designed to endure in demanding environments.

Lifetime Warranty, \$20K Ultimate Lifetime Insurance and Environmentally Responsible DesignThe SWIVEL6USB comes with a lifetime warranty and \$20,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only). It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

Specifications

OVERVIEW	
UPC Code	037332210944
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Length Details	Direct plug-in
Voltage Compatibility (VAC)	120
Maximum Surge Amps	60000
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	0
Right-Angle Plug	No
Input Cord Length (m)	0.00
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Outlet Orientation	Rotatable
Right-Angle Outlets	No



USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Built-in LEDs confirm suppressor "protected" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1200
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
UL1449 Let Through Rating	800, 800, 800
EMI / RFI Filtering	150 kHz to 100 mHz
Automatic Shut-Off	No
CHARGING	
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 3.1A
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Antimicrobial	No
Housing Color	Black
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	29mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	19.20 x 11.40 x 5.79
Shipping Dimensions (hwd / in.)	7.56 x 4.49 x 2.28
Shipping Weight (kg)	0.33
Shipping Weight (lbs.)	0.72
Unit Dimensions (hwd / in.)	5.47 x 3.94 x 2.28
Unit Weight (kg)	0.00



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Unit Weight (lbs.)	0.00
FEATURES & SPECIFICATIONS	
Rotatable Outlets	Yes
STANDARDS & COMPLIANCE	
Canada	Approved for Canada by ETL
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	Tested to UL1449 3RD EDITION Requirements by ETL
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>