

## FC to LC 62.5/125 Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: T020-001-LC62



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an LC connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

### Description

The T020-001-LC62 FC to LC 10 Gb Adapter converts a native FC fiber female port on the Tripp Lite T020-001-PSF Multi-Function Optical Fiber Cable Tester to an LC female port for 62.5/125 multimode cable testing. "62.5/125" is clearly labeled on the unit to differentiate the T020-001-LC62 from other adapters. Included dust caps keep the connectors clean when not in use.

### Features

#### Converts Cable Tester's FC Connector to an LC Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 62.5/125 multimode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

## Specifications

OVERVIEW	
UPC Code	037332197658
Technology	Multimode
PHYSICAL	
Color	Beige; Silver
Clad Diameter (microns)	125

### Highlights

- Converts native FC jack to an LC female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 62.5/125 multimode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

### System Requirements

- Tripp Lite T020-001-PSF Multi-Function Optical Fiber Cable Tester

### Package Includes

- T020-001-LC62 FC to LC 62.5/125 Adapter

# TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

Core Diameter (microns)	62.5
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

# TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.