

Safe-IT 6-Port USB Charging Station - 2x USB-C 60W, 4x USB-A, 2x 5-15R, Wireless Charging, 1000 Joules, 10 ft. Cord, Antimicrobial Protection

MODEL NUMBER: TLM210CAM



Highlights

- 5V USB-A ports (2x 2.4A, 2x 2.1A) provide charging power for smartphones and tablets
- USB-C Quick Charge port provides up to 60W of charging power to compatible devices
- Dual 10W wireless charging areas avoid cable clutter when charging smartphones
- 1000 joules protect your valuable electronics against dangerous surges and spikes
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- TLM210CAM 6-Port USB Charging Station
- Owner's manual

Features 6 USB charging ports, 2 AC outlets and 2 wireless pads for keeping laptops, smartphones and other devices ready for use.

Features

Flexible USB Charging Station Powers and Charges Up to 10 Devices at the Same Time

At home or in the office, this desktop charging station provides enough power and ports to keep your devices at high capacity. No more peering behind furniture to find an available outlet or unplugging one device to charge another. This metal charging station is ideal for homes with busy families, dorm rooms, conference rooms and offices with multiple mobile devices. It powers and charges up to 10 devices at the same time, including smartphones, tablets, laptops and e-readers. It doesn't require a computer, so you can take it anywhere AC power is available.

Provides Plenty of Power to Keep Your Devices at Capacity

Two USB-A ports provide a maximum of 5V 2.4A (12W) of power and two more USB-A ports provide up to 5A 2.1A (10.5W), enough for fast-charging most smartphones and tablets. Two USB-C Quick Charge ports provide up to 60W for battery-intensive devices like the MacBook Pro or Chromebook Pixel.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, wireless router, desk lamp or other home/office electronics into two NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. A surge protection rating of 1000 joules defends your valuable electronic components. EMI/RFI filtering helps your connected equipment perform better and last longer.

Wireless Charging Pads Deliver Power to Phones

Who wants to mess with tangled cables when you just want to charge your smartphone? Two 10W charging areas make the process easier by charging wirelessly. Just place your phones against the charging surfaces for convenient charging.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The Safe-IT™ charging station features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Bold Triangle Desktop Design Gives You Plenty of Options for Placement and Use

The TLM210CAM offers one NEMA 5-15R outlet, one USB-C port and two USB-A ports on each side,

making it ideal for shared workspaces, such as conference room tables. The 10-foot braided power cord with NEMA 5-15P plug connects to any standard AC wall outlet.

Specifications

OVERVIEW	
UPC Code	037332271877
Product Type	Surge Protector
Charging Form Factor	Charging Hub
Device Compatibility	Amazon Kindle; Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Cord Gauge (AWG)	14
Maximum Surge Amps	1000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	12
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
CHARGING	
Number of Charging Ports	6
Charging Method	USB
Charging Port Type	(4) USB A (FEMALE); (2) USB C (FEMALE)
Charging Ports / Amps	(2) 2.1A; (2) 2.4A; (3) 3.1A
Overcharge Protection	Yes

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1000
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	300,300,300
EMI / RFI Filtering	41.09dB
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Steel
Power Cord Color	Black and White Braided Cord
Mounting Holes or Slots	Yes
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	7.87 x 17.13 x 7.48
Shipping Dimensions (hwd / cm)	19.99 x 43.51 x 19.00
Shipping Weight (lbs.)	7.61
Shipping Weight (kg)	3.45
Unit Dimensions (hwd / in.)	4.290 x 14.790 x 4.850
Unit Dimensions (hwd / cm)	39.7 x 12.99 x 0.00
Unit Weight (lbs.)	1.8
Unit Weight (kg)	0.82
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
GaN Technology	No
Angled Plug	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 60950-1 (Canada); UL 60950-1

TRIPP·LITE

by **EAT·N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance

TRIPP·LITE

by **EAT·N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.