

## Protect It! 6-Outlet Industrial Safety Surge Protector, 9-ft. Cord, 1500 Joules, Cord Wrap, Hang Holes

MODEL NUMBER: TLM609SA



### Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 9 ft. cord
- 1500 joule rating
- Cord wrap with hang holes
- Rugged metal case

### Package Includes

- TLM609SA Safety Surge Suppressor
- 4 safety covers
- Owner's manual

### Description

This Tripp Lite surge suppressor is designed to provide safe, reliable surge protection in harsh environments. A high 1500 joule rating can protect connected equipment against even the strongest surges. 6 outlets protect connected equipment against damaging surges, spikes and line noise. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 9 ft. grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Protected LED confirms that connected equipment is being protected. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$50,000 and for life! As an added safety feature, the surge suppressor's bright yellow color alerts you and others that power cords and tools are in use.

### Features

- 6 outlets protect connected equipment against damaging surges, spikes and line noise
- 9-ft. cord with integrated cord clip reaches distant outlets
- Lighted ON/OFF switch with integrated circuit breaker provides power control over connected equipment; Breaker protects against dangerous system overload
- Protected LED - If this green LED ever goes out, Tripp Lite will replace your surge suppressor under warranty at no charge!
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets
- 4 safety covers shield unused outlets from debris and accidental contact
- Rugged metal case stands up to the harshest environments
- Cord wrap with hang holes provides convenient cord management
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.



- 1500 joules of surge protection
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

## Specifications

| OVERVIEW                           |  |
|------------------------------------|--|
| UPC Code                           | 037332140098                           |
| INPUT                              |  |
| Nominal Input Voltage(s) Supported | 120V AC                                |
| Recommended Electrical Service     | 120V (110-125V)                        |
| Input Cord Gauge Type              | 14 gauge; SJT                          |
| Voltage Compatibility (VAC)        | 120                                    |
| Maximum Surge Amps                 | 60000                                  |
| Input Plug Type                    | NEMA 5-15P                             |
| Input Cord Length (ft.)            | 9                                      |
| Right-Angle Plug                   | No                                     |
| Input Cord Length (m)              | 2.74                                   |
| Integrated Cord Clip               | Yes                                    |
| OUTPUT                             |  |
| Frequency Compatibility            | 60 Hz                                  |
| Output (Watts)                     | 1800                                   |
| Output Receptacles                 | (6) 5-15R                              |
| Circuit Breaker (amps)             | 15                                     |
| Overload Protection                | Combo power switch and circuit breaker |
| Transformer Accommodation          | (4) Yes                                |
| Outlet Orientation                 | 1 single row of 6                      |
| Right-Angle Outlets                | No                                     |
| USER INTERFACE, ALERTS & CONTROLS  |  |
| Diagnostic LED(s)                  | Yes                                    |



|  |   |
|--|---|
| Switches   | Combination AC circuit breaker and 2 position lighted on/off power switch                             |
| Diagnostic LED Details                               | 1 green "protected" LED confirms surge suppression is present   |
| <b>SURGE / NOISE SUPPRESSION</b>                     |   |
| AC Suppression Joule Rating                          | 1500  |
| AC Suppression Response Time                         | < 1 ns  |
| Protection Modes                                     | Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression                      |
| Clamping Voltage (RMS)                               | 150   |
| EMI / RFI Filtering                                  | Up to 20 dB   |
| Automatic Shut-Off                                   | Yes   |
| <b>DATALINE SURGE SUPPRESSION</b>                    |   |
| Telephone/DSL Protection                             | No  |
| Cable (Coax) Protection                              | No  |
| Network (Ethernet) Protection                        | No  |
| <b>PHYSICAL</b>                                      |   |
| Antimicrobial Coating                                | No  |
| Color  | Black; Yellow   |
| Color (AC Line Cord)                                 | Yellow  |
| Integrated Keyhole Mounting Slots                    | Yes   |
| Keyhole Slot Mounting Measurement (Center to Center) | 209.55mm  |
| Material of Construction                             | Metal   |
| Outlets Measurement (Center to Center)               | Distance between standard outlets = 30.40mm; Distance between standard and transformer outlets = 45mm |
| Receptacle Color                                     | Black   |
| Shipping Dimensions (hwd / cm)                       | 40.89 x 6.10 x 17.78  |
| Shipping Dimensions (hwd / in.)                      | 16.10 x 2.40 x 7.00   |
| Shipping Weight (kg)                                 | 1.45  |
| Shipping Weight (lbs.)                               | 3.20  |
| Unit Dimensions (hwd / cm)                           | 40.56 x 7.80 x 4.09   |
| Unit Dimensions (hwd / in.)                          | 15.97 x 3.07 x 1.61   |
| Unit Weight (kg)                                     | 1.23  |
| Unit Weight (lbs.)                                   | 2.71  |
| <b>SPECIAL FEATURES</b>                              |   |
| Rotatable Outlets                                    | No  |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

| <b>STANDARDS &amp; COMPLIANCE</b>                          |   |
|--|---|
| Canada   | cUL   |
| Approvals  | cULus, RoHS   |
| UL1449 3rd Edition (AC Suppression)                        | UL1449 3rd Edition  |
| <b>WARRANTY</b>  |   |
| Product Warranty Period (Worldwide)                        | Lifetime limited warranty   |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$50,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a> |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>