

Power It! 8-Outlet Safety Power Strip, 12 ft. (3.66 m) Cord with GFCI Plug

MODEL NUMBER: TLM812GF



Highlights

- 8 outlets (including transformer outlets and 4 safety covers)
- 12-ft. (3.66 m) cord with GFCI plug
- Cord wrap with hang holes
- Rugged metal case

Package Includes

- TLM812GF Safety Power Strip
- 4 safety covers
- Owner's manual

Description

This Tripp Lite power strip is designed to safely distribute power to connected equipment in harsh environments. It provides a convenient source for multiple outlets wherever they're needed. 8 outlets distribute AC power to a wide range of power tools, pumps, machinery, air compressors and more. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 12-ft. (3.66 m) grounded cord with integrated cord clip reaches distant outlets. A GFCI plug protects users from electrical shock in wet or humid environments. A lighted on/off switch provides power control over connected equipment. 4 safety covers shield unused outlets from debris and accidental contact. A rugged metal case stands up to the harshest environments. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Its bright yellow color alerts you and others that power cords and tools are in use.

Features

- 8 outlets distribute AC power to a wide range of power tools, pumps, machinery, air compressors and more.
- Convenient transformer outlets accommodate multiple transformers without blocking other outlets.
- A 12-ft. (3.66 m) grounded cord with integrated cord clip reaches distant outlets.
- A GFCI plug protects users from electrical shock in wet or humid environments.
- A lighted on/off switch with integrated 15 amp circuit breaker provides power control and overload protection over connected equipment.
- 4 safety covers shield unused outlets from debris and accidental contact.
- A rugged metal case stands up to the harshest environments.
- Built-in cord wrap with hang holes provides convenient cord management.
- Integrated keyhole slots on bottom panel provide convenient wall/desk mounting.
- Its bright yellow color alerts you and others that power cords and tools are in use.
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.

Specifications



OVERVIEW	
UPC Code	037332140135
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V, 15A
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	12
Right-Angle Plug	No
Input Cord Length (m)	3.66
Integrated Cord Clip	Yes
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(8) 5-15R
Circuit Breaker (amps)	15
Overload Protection	GFCI plug
Transformer Accommodation	(6) Yes
Outlet Orientation	1 bank of 5, 1 bank of 3 (transformer outlets)
Right-Angle Outlets	Yes
Outlet Safety Covers Detail	Includes 4 outlet safety covers
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
PHYSICAL	
Material of Construction	Metal
Color	Yellow; Black
Power Cord Color	Yellow
Housing Color	Yellow; Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	145mm



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Outlets Measurement (Center to Center)	Distance between standard outlets = 25.40mm; Distance between transformer outlets = 50.80mm
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	6.35 x 25.40 x 37.59
Shipping Dimensions (hwd / in.)	2.50 x 10.00 x 14.80
Shipping Weight (kg)	1.63
Shipping Weight (lbs.)	3.60
Unit Dimensions (hwd / in.)	10.26 x 5.13 x 1.57
Unit Dimensions (hwd / cm)	26.06 x 13.03 x 3.99
Unit Weight (lbs.)	4.63
Unit Weight (kg)	2.10
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>