

## Protect It! 11-Outlet Surge Protector - 5-15R Outlets, 4200 Joules, 2 USB Charging Ports, 8 ft. (2.4 m) Braided Cord, Black

MODEL NUMBER: TLP118DBUC



Protects your home, office and small electronics against the harmful effects of surges, spikes and line noise.

### Features

#### 11-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home, office or retail workstation, this Protect It!® surge protector features a surge protection rating of 4200 joules to defend your valuable electronic components against power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP118DBUC protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

#### NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your computer, printer, router, desk lamp or other home/office electronics into 11 NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Six outlets are spread apart to allow connection of bulky transformers without blocking adjacent outlets.

#### 2 USB Ports Share 4 Amps of Charging Power

This surge protector with one USB-A charging port and one USB-C charging port is ideal for keeping your devices at full battery capacity. The USB ports are available for charging your smartphone, tablet and other mobile devices.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Safety Features Help Maintain Your Equipment's Well-Being

A side-mounted on/off switch allows easy one-touch control over all equipment connected to the TLP118DBUC. An integrated 15A resettable circuit breaker helps prevent equipment damage by cutting power to outlets if the protection circuit is incapacitated. Diagnostic LEDs let you know that your equipment is protected and grounded. The ABS plastic housing is fire-retardant to provide extra safety and durability.

#### Flexible Installation Options

Place the TLP118DBUC on any flat surface in your home, office, workbench or anywhere else you need power for your equipment. Integrated rear keyhole slots accommodate wall or desktop mounting. The

### Highlights

- 11 NEMA 5-15R outlets distribute AC power to connected home/office/work equipment
- 4200 joules protect your valuable electronics against dangerous surges and spikes
- USB ports share 4A for fast charging of phones, tablets and other mobile devices
- 8 ft. braided input cord with NEMA 5-15P plug connects to compatible AC wall outlet
- On/off switch with circuit breaker allows one-touch control over connected equipment

### Package Includes

- TLP118DBUC 11-Outlet Surge Protector
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

eight-foot (2.4-meter) braided input cord with NEMA 5-15P right-angle plug reaches a nearby outlet to fit easily into your workstation or home theater setup.

## Specifications

OVERVIEW	
UPC Code	037332294074
Product Type	Surge Protector
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	8
Right-Angle Plug	No
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(11) 5-15R
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	(1) Yes
Outlet Orientation	two rows of 11 outlets total
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LED confirms suppressor "protection present" (green) status
CHARGING	



Powering Business Worldwide

TRIPP LITE  
SERIES

Number of Charging Ports	2
Total Charging Amps	4
Charging Port Type	(1) USB A (FEMALE); (1) USB C (FEMALE)
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	4200
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500V
EMI / RFI Filtering	Yes
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	1.70 x 8.10 x 14.40
Shipping Dimensions (hwd / cm)	4.32 x 20.57 x 36.58
Shipping Weight (lbs.)	1.70
Shipping Weight (kg)	0.77
Unit Dimensions (hwd / in.)	1.420 x 4.800 x 13.000
Unit Dimensions (hwd / cm)	1.42 x 4.8 x 13
Unit Weight (lbs.)	1.2
Unit Weight (kg)	0.54
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 104°F (-15° to 40°C)
Operating Humidity Range	20% to 85% RH
Storage Humidity Range	0% to 90% RH



Powering Business Worldwide

TRIPP LITE  
SERIES

FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); UL 1363; UL 1449
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.