

## Protect It! 12-Outlet Surge Protector, 8 ft. (2.43 m) Cord, 4320 Joules, Tel/Modem/Coax Protection, 2 USB Ports, Black

MODEL NUMBER: TLP128TTUSBB



12-outlet surge protector safeguards your home/office electronics against dangerous surges, spikes and line noise.

### Features

**12-Socket Surge Protector Safeguards Your Sensitive Electronics**Ideal for your home or office workstation, this Protect It!® 12-outlet surge protector features a surge protection rating of 4320 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP128TTUSBB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

**NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices**Plug your PC, printer, scanner, router, modem, television, stereo receiver and other home/office electronics into 12 NEMA 5-15R AC outlets to protect them against dangerous surges, spikes and line noise. Six outlets are designed for greater flexibility in placing connected devices or accepting bulky transformers without blocking adjacent outlets. The eight-foot AC power cord with space-saving right-angle NEMA 5-15P plug helps you connect the surge protector to a wall outlet located behind furniture.

**Also an RJ11 and Coaxial Cable Surge Protector to Cover All Your Bases**Built-in RJ11 jacks and silver coaxial cable connectors allow connection of telephone, fax, modem, cable television and satellite equipment. The TLP128TTUSBB prevents dangerous “back door” power surges from damaging your data line components.

**2 USB Ports Share 2.1 Amps of Charging Power**Dual USB-A ports are available for charging your smartphone, tablet and other USB mobile devices, which are also protected from the damaging effects of surges, spikes and line interference.

**Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better**Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This 12-socket surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better with longer lifespans.

### Highlights

- 12 total NEMA 5-15R outlets—6 are designed to accommodate bulky transformers
- 4320 joules protect your valuable electronics against dangerous surges/spikes/line noise
- RJ11 and coaxial cable connectors protect phone/fax/modem/cable/satellite equipment
- 2 USB ports share 2.1A for fast charging of phone, laptop and other mobile devices

### Applications

- Protecting computers, modems, home theater equipment and other valuable electronics against AC power surges and spikes
- Filtering potentially damaging line noise to improve connected equipment's performance and lifespans
- Charging a smartphone, tablet or other USB devices via the dual USB ports

### Package Includes

- TLP128TTUSBB Protect It! 12-Outlet Surge Protector
- Owner's manual

**Includes the Latest Safety Features**The lighted on/off switch provides one-touch control over connected equipment. Diagnostic LEDs confirm your wall outlet is properly grounded and your connected equipment is protected. Its high-impact plastic housing is designed to endure in demanding environments.

**Lifetime Warranty, \$150K Ultimate Lifetime Insurance and Environmentally Responsible Design**The TLP128TTUSBB comes with a lifetime warranty and \$150,000 of Ultimate Lifetime Insurance for any connected components damaged by a power surge (U.S., Canada and Puerto Rico only). It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

## Specifications

OVERVIEW	
UPC Code	037332209788
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Plug Features	Right Angle
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	8
Right-Angle Plug	Yes
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(12) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(7) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	

Diagnostic LED(s)	Yes
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Watts	10.5
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A
Overcharge Protection	No
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	4320
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	800/800/800
EMI / RFI Filtering	Up to 40 dB
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	1 line
Network (Ethernet) Protection	No
Telephone/DSL Protection	Yes
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between horizontal tabs = 75 mm; Distance between vertical tabs = 41.6 mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	15.90 x 8.10 x 1.80

Shipping Dimensions (hwd / cm)	40.39 x 20.57 x 4.57
Shipping Weight (lbs.)	2.34
Shipping Weight (kg)	1.06
Unit Dimensions (hwd / in.)	13.580 x 7.870 x 1.380
Unit Dimensions (hwd / cm)	12.34 x 31.50 x 3.84
Unit Weight (lbs.)	1.90
Unit Weight (kg)	0.86
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
GaN Technology	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 269.3 (Canada); CAN/CSA-C22.2 No. 308 (Canada); cUL Listed; NOM (Mexico); UL 1449; UL 1363; UL Listed
Product Compliance	FCC Part 68; RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000&nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;