

## Protect It! In-Desktop Power Grommet - NEMA 5-15P, 2x USB-A Charging, Surge Protection, 10 ft. Cord, Antimicrobial, Black

MODEL NUMBER: TLP12POAM



### Highlights

- Pushes down out of the way flush with desktop surface when not in use
- NEMA 5-15R outlet distributes AC power to connected home/office equipment
- 2 USB-A ports share 4.2A for fast charging of phones and other mobile devices
- 1000 joules protect your valuable electronics against dangerous surges and spikes
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

### Package Includes

- TLP12POAM 1-Outlet Pop-Up Power and Charging Dock
- Owner's manual

Installs in your desktop's pre-cut grommet to charge and power up to 3 devices at the same time.

### Features

#### Fits into Your Desktop Grommet for Reliable Power and Charging

This Protect It!® dock is designed for installation in your desktop's pre-cut three-inch grommet hole. When not being used to power or charge devices, you can push down the TLP12POAM into the grommet and flush against the desktop's surface to save valuable space. To connect devices, simply pop it up out of the hole. This Pop-Up Power and Charging Dock is ideal for home and office workstations with limited desk space.

#### USB Ports and NEMA 5-15R Outlet Accept a Wide Range of Electronic Devices

One NEMA 5-15R outlet and two USB-A ports (4.2A combined) are available for powering and charging your laptop, tablet, smartphone or other devices. The outlet features a 1000 joule rating to defend its connected computer, printer or other valuable equipment against damaging power surges and spikes. The 10-foot (3-meter) input cord with right-angle plug connects to a compatible AC wall outlet.

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive EMI (electromagnetic interference) and RFI (radio frequency interference) line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

#### Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Environment

The TLP12POAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

## Specifications

OVERVIEW	
UPC Code	037332271884
Product Type	Surge Protector

Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Input Plug Features	Right Angle
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	10
Right-Angle Plug	Yes
Input Cord Length (m)	3.05
Integrated Cord Clip	No
<b>OUTPUT</b>	
Output Receptacles	(1) 5-15R
Circuit Breaker (amps)	12
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	No
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Amps	4.2A
Total Charging Watts	12
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports / Amps	(2) 2.1A
Overcharge Protection	No
Charging Amps per Port	2.1A
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1000

AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	300,300,300
EMI / RFI Filtering	Yes
Automatic Shut-Off	No
<b>DATALINE SURGE SUPPRESSION</b>	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Plug Color	Black
Power Cord Color	Black
Mounting Location	Desktop
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	8.27 x 5.12 x 3.94
Shipping Dimensions (hwd / cm)	21.01 x 13.00 x 10.01
Shipping Weight (lbs.)	1.76
Shipping Weight (kg)	0.80
Unit Dimensions (hwd / in.)	3.350 x 3.540 x 2.980
Unit Dimensions (hwd / cm)	3.35 x 3.54 x 2.98
Unit Weight (lbs.)	1.54
Unit Weight (kg)	0.70
Input Cord Color	Black
Mounting Details	Fits 3.15-inch (80mm) standard desktop grommet hole
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	Yes
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	CAN/CSA-C22.2 No. 308 (Canada); UL 962A; UL Listed; cUL Listed
Product Compliance	RoHS

# TRIPP·LITE

by **EAT·N**

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States

WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$15,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

# TRIPP·LITE

by **EAT·N**

© 2023 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.