

Safe-IT 30W 2-Outlet Surge Protector - 5-15R Outlets, 3 USB Ports, 6 ft. (1.8 m) Cord, 300 Joules, Antimicrobial Protection, White

MODEL NUMBER: TLP26PD30WCAM



Safely charges and powers up to 5 devices, including laptops and tablets, during important workplace meetings and conferences.

Features

2-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or travel use, the TLP26PD30WCAM features a surge suppression rating of 300 joules to defend your sensitive electronic components against power surges and spikes.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptops, projector, printer and other conference-table electronics into two NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The outlets are spaced widely apart to accept bulky transformers without blocking any outlets or ports.

USB Ports Allow Safe and Rapid Charging

Two USB-A ports are available for charging your smartphones, tablets and other USB mobile devices. They share 4.8A of charging power, which is plenty for delivering ample power to demanding devices. A USB-C PD 3.0 port delivers 18W of charging power for laptops and other larger devices. All three ports share 30W maximum.

Filtering EMI/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT™ TLP26PD30WCAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Compact Round Design Gives You Plenty of Options for Installation and Use

Just four inches in diameter, the TLP26PD30WCAM fits easily into your home or office workspace, providing power and USB charging at your fingertips. Its compact design also makes the surge protector ideal for travel, fitting easily into your backpack, laptop bag or suitcase for use in hotels, conference rooms and cruise ships. The six-foot (1.8-meter) braided power cord connects to an AC wall outlet.

Highlights

- 2 NEMA 5-15R outlets are spaced apart to accommodate bulky transformers
- 300 joules protect your valuable electronics against dangerous surges and spikes
- 2 USB-A ports share 4.8A for fast charging of phones, tablets and other mobile devices
- USB-C PD 3.0 charging port delivers 18W of charging power for laptops
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- TLP26PD30WCAM 2-Outlet Surge Protector
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332274915
Device Compatibility	Laptop; Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Plug Features	Right Angle
Input Cord Gauge Type	16 gauge
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(2) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
CHARGING	
Number of Charging Ports	3
Total Charging Watts	30
Charging Method	USB
Charging Port Type	(2) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports Details	2 x USB-A (2.4A) charging ports for Phones, laptops, and other devices 1 x USB-C 3A PD Charging Port for fast charging
Charging Ports / Amps	(1) 3A / 2A / 1.5A; (2) 4.8A
Overcharge Protection	No

SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	300
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Plug Color	White
Wire Gauge (AWG)	16
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	No
Receptacle Color	White
Shipping Dimensions (hwd / in.)	2.60 x 4.60 x 6.30
Shipping Dimensions (hwd / cm)	6.60 x 11.68 x 16.00
Shipping Weight (lbs.)	1.10
Shipping Weight (kg)	0.50
Unit Dimensions (hwd / in.)	4.170 x 4.170 x 1.180
Unit Dimensions (hwd / cm)	10.59 x 10.59 x 3
Unit Weight (lbs.)	1.18
Unit Weight (kg)	0.54
Rubber Feet	Yes
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	Yes
GaN Technology	No

TRIPP-LITE

by **EAT•N**

1000 Eaton Boulevard
Cleveland, OH 44122
United States

STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 21 (Canada); ICES (Canada); UL 817
Product Compliance	FCC Part 15 Class B (USA); RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 & Ultimate Lifetime Insurance

TRIPP-LITE

by **EAT•N**

© 2023 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.