

Protect It! 230V Surge Protector with 2 French/Belgian Outlets, 0.33M Cord, 380 Joules, French plug

MODEL NUMBER: TLP2USBF



Highlights

- 2 safety outlets
- 380 joule rating
- 2 USB ports
- 33 cm cord

Package Includes

- TLP2USBF surge suppressor
- Instruction manual and warranty information

Description

Tripp Lite's Protect It!™ TLP2USBF offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP2USBF offers 2 French Type E outlets and 33 cm AC line cord. 2 USB ports are perfect for charging cell phones, iPods, MP3 players and other mobile devices. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP2USBF offers economical AC surge suppression
- 380 joules AC surge suppression shields equipment from surges and line noise
- 2 French type E outlets protect computers and peripherals
- 2 USB ports are perfect for charging cell phones, iPods, MP3 players and other mobile devices
- 33 cm cord with French plug
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145475
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	French



Powering Business Worldwide



Input Cord Length (ft.)	1
Right-Angle Plug	Yes
Input Cord Length (m)	0.30
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(2) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	(1) Yes
CONNECTIONS	
Number of Ports	2
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	No
CHARGING	
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	380
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Black
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	No
Receptacle Color	Gray
Shipping Dimensions (hwd / in.)	2.00 x 7.60 x 7.40
Shipping Dimensions (hwd / cm)	5.08 x 19.30 x 18.80
Shipping Weight (lbs.)	0.70



Powering Business Worldwide



Shipping Weight (kg)	0.32
Unit Dimensions (hwd / in.)	5.900 x 2.165 x 1.634
Unit Dimensions (hwd / cm)	14.99 x 5.51 x 4.14
Unit Weight (lbs.)	.48
Unit Weight (kg)	0.22
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.