

Protect It! 3-Outlet Surge Protector with Desk Clamp, 10 ft. Cord, 510 Joules, 2 USB Charging Ports, Black Housing

MODEL NUMBER: TLP310USBC



Clamps safely to your workstation to safeguard your computer, scanner and other electronics against surges, spikes and line noise, as well as charge mobile devices, including smartphones, tablets and MP3 players.

Description

The TLP310USBC Protect It!® 3-Outlet Surge Protector features three NEMA 5-15R outlets and a surge suppression rating of 510 joules to protect your components against surges, spikes and EMI/RFI line noise that can damage sensitive electronics and destroy data. Plus, two USB ports produce 3.1A of combined power to charge your mobile devices, such as smartphones, tablets and MP3 players.

Recommended for home, office, workstations, dorms and hotel rooms, the TLP310USBC mounts permanently to a clamp that attaches to most desks, tables and flat surfaces. The 10-foot power cord fits through the back of the clamp to reduce cable clutter. A top storage shelf holds smartphones and other small devices while they're charging.

Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$20,000 for life (valid in the U.S., Canada and Puerto Rico only).

Features

Powers and Protects Electronic Components

- 3 NEMA 5-15R outlets accept most computers and peripherals
- 510 joules of surge suppression protect against surges, spikes and EMI/RFI line noise
- Recommended for home, office, workstations, dorms and hotel rooms

Powers and Charges Mobile Devices

- 2 USB ports (3.1A total) charge smartphones, tablets and other devices

Highlights

- Clamp attaches firmly to most desks, tables and flat surfaces
- 3 NEMA 5-15R outlets and 2 USB charging ports (3.1A total)
- 510 joules of surge suppression
- 10 ft. power cord reaches distant AC outlets

Package Includes

- TLP310USBC Protect It! 3-Outlet Surge Protector
- Desk clamp
- Mounting hardware
- Owner's manual



- Top storage shelf accommodates smaller mobile devices during charging

Clamps Safely to Most Flat Surfaces

- Attaches permanently to adjustable clamp that fits most desks, tables and workstations
- 10 ft. AC power cord fits through back of clamp to avoid cable clutter

\$20,000 Ultimate Lifetime Insurance

- Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$20,000 for life
- Valid in the U.S., Canada and Puerto Rico only

Specifications

OVERVIEW	
UPC Code	037332198464
Product Type	Surge Protector
Charging Form Factor	Strip
Device Compatibility	Phone; Tablet; Amazon Kindle
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Length Details	Strip
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(2) Yes
Right-Angle Outlets	No



USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	510
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	1000
UL1449 Let Through Rating	1000
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	No
CHARGING	
Charging Ports / Amps	(2) 3.1A
Number of Charging Ports	2
Charging Method	USB
Charging Port Type	USB A (FEMALE)
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Antimicrobial Coating	No
Color	Black
Color (AC Line Cord)	Black
Housing Color	Black
Included Mounting Accessories	Mounting hardware
Integrated Keyhole Mounting Slots	No
Material of Construction	Plastic
Receptacle Color	Black
Shipping Dimensions (hwd / cm)	20.83 x 10.92 x 13.21
Shipping Dimensions (hwd / in.)	8.20 x 4.30 x 5.20
Shipping Weight (kg)	1.18



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	2.60
Unit Dimensions (hwd / cm)	4.93 x 4.47 x 14.7
Unit Dimensions (hwd / in.)	1.94 x 1.76 x 5.8
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449, UL962A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$20,000 Ultimate Lifetime Insurance

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>