

3-Outlet Spherical Surge Protector, 4 USB Ports (4.8A Shared) - 6-ft. (1.83 m) Cord, 5-15P Plug, 540 Joules, Black

MODEL NUMBER: TLP36USB



Portable ball-shaped surge protector with USB charging safeguards your electronics against dangerous surges, spikes and line noise.

Features

Sphere-Shaped 3-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or travel use, this Protect It!® three-outlet power ball features a surge suppression rating of 540 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP36USB protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

3 NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptop, external hard drive, desk lamp or other home/office devices into the NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The outlets are located on different sides to allow easy connection of bulky transformers.

4 USB Ports Share 4.8 Amps of Charging Power

USB-A ports are available for charging your smartphone, tablet and other USB mobile devices. They share 4.8A for charging multiple devices at the same time.

Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems. This surge protector filters out disruptive line noise that can disturb your electronics and inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Includes the Latest Safety Features to Maintain Your Equipment's Well-Being

Automatic shutoff permanently cuts power to outlets if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. Safety shutters on unused outlets help prevent electrical shock. A green LED confirms your connected equipment is protected. Mounting slots allow installation on any flat surface.

Ball-Shaped Design Gives You Plenty of Options for Installation and Use

Less than four inches in diameter, the spherical TLP36USB fits easily into your home or office workspace, providing power and USB charging at your fingertips. Its compact design also makes the surge protector ideal for travel, fitting easily into your backpack, laptop bag or suitcase for use in hotels, conference rooms and cruise ships.

Highlights

- 3 NEMA 5-15R outlets for powering a laptop, smartphone or other electronic devices
- 540 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports share 4.8A for fast charging of phones, tablets and other mobile devices
- Ball-shaped design takes up little room on your desk and easily packs away for travel

Applications

- Protect a laptop, external hard drive or other valuable electronics against AC power surges and spikes
- Filter potentially damaging line noise to improve connected equipment's performance and lifespan
- Safeguard valuable data against damage stemming from unexpected surges
- Charge a smartphone and tablet without taking up available AC outlets

Package Includes

- TLP36USB 3-Outlet Surge Protector Ball, Black
- Owner's manual

Specifications



OVERVIEW	
UPC Code	037332260253
Device Compatibility	Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	6
Right-Angle Plug	No
Input Cord Length (m)	1.83
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	1 Green LED - Protection
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
CHARGING	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Charging Ports / Amps	(4) 4.8A
Number of Charging Ports	4
Charging Method	USB
Charging Port Type	USB A (FEMALE)
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Black
Antimicrobial Coating	No
Color (AC Line Cord)	Black
Housing Color	Black
Integrated Keyhole Mounting Slots	yes
Material of Construction	Plastic
Receptacle Color	Black
Unit Dimensions (hwd / cm)	9.1 x 9.0 x 8.4
Unit Dimensions (hwd / in.)	3.59 x 3.56 x 3.32
Unit Weight (kg)	0.54
Unit Weight (lbs.)	1.18
SPECIAL FEATURES	
Rotatable Outlets	No
STANDARDS & COMPLIANCE	
United States	Safety US - UL1363:2018(5th Ed); UL1449:2014(4th ED) R7.17
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$50,000 Ultimate Lifetime Insurance



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>