

Safe-IT 3-Outlet Spherical Surge Protector, 5-15R Outlets, 4 USB Charging Ports, 8 ft. (2.4 m) Cord, Antimicrobial Protection

MODEL NUMBER: TLP38UAM



Highlights

- 3 NEMA 5-15R outlets are spaced apart to accommodate bulky transformers
- 540 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports share 4.8A for fast charging of phones, tablets and other mobile devices
- Ball shape takes up little room on your conference table and easily packs away for travel
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- TLP38UAM 3-Outlet Surge Protector Ball
- Owner's manual

Safely charges and powers up to 7 devices, including laptops and tablets, during important workplace meetings and conferences.

Features

Sphere-Shaped 3-Outlet Surge Protector Safeguards Your Sensitive Electronics

Ideal for your home or office workstation or travel use, this Safe-IT™ power ball features a surge suppression rating of 540 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP38UAM protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptops, projector, printer and other conference-table electronics into three NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. The outlets offer easy 360-degree access to power and are located on different sides to accept bulky transformers without blocking adjacent outlets.

USB Ports Share 4.8 Amps of Charging Power

Four USB-A ports are available for charging your smartphones, tablets and other USB mobile devices. They share 4.8A of charging power, which is plenty for delivering ample power to demanding devices.

Filtering EM/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT TLP38UAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Premium Safety Features Protect Your Valuable Equipment

Automatic shutoff permanently cuts power to outlets if the protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. Safety shutters on unused outlets help prevent electrical shock. A green LED confirms your connected equipment is protected. Mounting slots allow

permanent installation on any flat surface.

Compact Spherical Design Gives You Plenty of Options for Installation and Use

Less than four inches in diameter, the spherical TLP38UAM fits easily into your home or office workspace, providing power and USB charging at your fingertips. Its compact design also makes the surge protector ideal for travel, fitting easily into your backpack, laptop bag or suitcase for use in hotels, conference rooms and cruise ships. Mounting slots allow permanent installation on any flat surface.

Specifications

OVERVIEW	
UPC Code	037332265784
Device Compatibility	Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	8
Right-Angle Plug	No
Input Cord Length (m)	2.44
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(3) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	No
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	1 Green LED - Protection
CHARGING	
Number of Charging Ports	4
Total Charging Amps	4.8A

Total Charging Watts	24
Charging Method	USB
Charging Port Type	USB A (FEMALE)
Charging Ports Details	2 x USB-A (2.4A) charging ports for iPhones and iPads 2 x USB-A (2.4A) charging ports for Android and other devices
Charging Ports	(2) 2.4A Quick Charge
Charging Ports / Amps	(4) 4.8A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Power Cord Color	Black
Mounting Holes or Slots	Yes
Receptacle Color	Black
Unit Dimensions (hwd / in.)	3.590 x 3.560 x 3.320
Unit Dimensions (hwd / cm)	9.1 x 9.0 x 8.4
Unit Weight (lbs.)	1.18
Unit Weight (kg)	0.54
Input Cord Color	Black
Mounting Details	Keyhole mounting slots in base
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No

Antimicrobial	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Product Certifications	UL 1449; UL 1363
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance