

Safe-IT Conference Power Surge Protector, 4 Rotating 5-15R Outlets, USB-C & 3 USB-A Ports, 10 ft. (3 m) Cord, Antimicrobial Protection

MODEL NUMBER: TLP410UCUFOAM



Safely charges and powers up to 8 devices, including laptops and tablets, during important workplace meetings and conferences.

Features

Keep Your Team's Devices Powered and Charged During Important Meetings

Workplace meetings involve a variety of devices – laptops, smartphones, tablets – to keep everyone coordinated and up to date with the information necessary to make important decisions. Guaranteeing those devices remain charged and powered is this Safe-IT™ Conference Power Surge Protector. Rounded to ensure equal access to everyone at the table, this UL-certified surge protector delivers ample power and reliable protection to as many as eight mobile devices at the same time.

NEMA 5-15R Outlets Accept a Wide Range of Electronic Devices

Plug your laptops, projector, printer and other conference-table electronics into four NEMA 5-15R outlets to protect them against dangerous surges, spikes and line noise. Each rotating outlet is located far enough apart from the others to accept bulky transformers without blocking adjacent outlets.

4 USB Ports Provide Plenty of Charging Power

One USB-C and three USB-A ports are available for charging your smartphones, tablets and other USB mobile devices. The USB-A ports share 4.8A of charging power, which is plenty for delivering ample power to demanding devices. The USB-C charging port supplies up to 3A.

Keeps Your Smart Speaker Fully Powered and at Your Disposal

A center device cradle is specially designed to fit an Amazon Echo Dot, Google Nest Mini or other smart speaker that allows access to instant information, external team members or just a little light thinking music. A built-in Micro-USB cable keeps the speaker powered.

1080 Joules Safeguard Your Sensitive Electronics

This surge protector features a surge suppression rating of 1080 joules to defend your sensitive electronic components against even the strongest power surges and spikes. Because residential power outlets have three wires—hot line (H), neutral (N) and ground (G)—the TLP410UCUFOAM protects all three, covering the two protection modes: full normal mode (H-N) and common mode (N-G/H-G).

Filtering EM/RFI Line Noise Helps Your Equipment Perform Better

This surge protector filters out disruptive electromagnetic and radio frequency interference that can inflict

Highlights

- 4 NEMA 5-15R rotating outlets designed to accommodate bulky transformers
- 1080 joules protect your valuable electronics against dangerous surges and spikes
- 4 USB ports supply power for fast charging of phones, tablets and other mobile devices
- Built-in Micro-USB cord powers Echo Dot, Google Mini or other smart speaker
- Antimicrobial protection helps resist the growth of bacteria, viruses, fungi, mold and mildew

Package Includes

- TLP410UCUFOAM Conference Power Surge Protector
- Owner's manual



hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

Antimicrobial Protection Helps Provide a Safer, Cleaner and Healthier Work Environment

The Safe-IT TLP410UCUFOAM features antimicrobial protection that helps resist the growth of bacteria, viruses, fungi, mold and mildew.

Premium Safety Features Protect Your Valuable Equipment

The on/off switch provides one-touch control over all connected equipment. Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required. A green LED confirms your connected equipment is protected.

Versatile Surge Protector Provides Flexible Installation Options

A 10-foot cord with NEMA 5-15P plug is long enough to give you plenty of options for placing the unit away from a wall outlet.

Specifications

OVERVIEW	
UPC Code	037332265777
Device Compatibility	Phone; Tablet
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Plug Features	Right Angle (36D)
Input Cord Gauge Type	14 gauge
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R
Circuit Breaker (amps)	15
Overload Protection	Yes (2-in-1 switch)
Transformer Accommodation	(4) Yes
Right-Angle Outlets	No



USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Yes
CHARGING	
Number of Charging Ports	4
Total Charging Amps	4.8A
Total Charging Watts	24
Charging Method	USB
Charging Port Type	(3) USB A (FEMALE); (1) USB C (FEMALE)
Charging Ports / Amps	(3) 2.4A; (1) 3A
Overcharge Protection	No
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
UL1449 Let Through Rating	500, 500, 600
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587/ANSI C62.41
Automatic Shut-Off	Yes
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Material of Construction	Plastic
Antimicrobial	Yes
Power Cord Color	White
Housing Color	White
Mounting Holes or Slots	No
Receptacle Color	White
Unit Dimensions (hwd / in.)	7.72 x 7.06 x 1.9
Unit Dimensions (hwd / cm)	19.3 x 17.6 x 4.9



Unit Weight (lbs.)	1.87
Unit Weight (kg)	0.85
FEATURES & SPECIFICATIONS	
Rotatable Outlets	No
GaN Technology	No
STANDARDS & COMPLIANCE	
Canada	CAN/CSA-22.2 No. 269.3:2007(3rd Ed.);CAN/CSA-C22.2 No.308-14
Approvals	RoHS
UL1449 3rd Edition (AC Suppression)	UL1449 4th Edition
UL1363 (Power Tap)	UL1363:2018 5th Edition
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 Ultimate Lifetime Insurance

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>