

Protect It! 230V Surge Protector with 5 French/Belgian Outlets, 1M Cord, 280 Joules, French plug, Diagnostic LED

MODEL NUMBER: TLP51F



Highlights

- 5 safety outlets
- 1 m cord
- "Protected" LED
- 280 joule rating

Package Includes

- TLP51F surge suppressor
- Instruction manual and product warranty information

Description

Tripp Lite's Protect It!™ TLP51F offers economical AC surge suppression for full protection of 220-250V home computers, printers, scanners, and desk lamps. The TLP51F offers 5 "French" Type E outlets and a 1 meter AC line cord. Internal safety covers protect against accidental contact with unused outlets.

Features

- Protect It!™ TLP51F offers economical AC surge suppression
- 280 joules AC surge suppression shields equipment from surges and line noise
- 5 "French" Type E outlets protect computers and peripherals
- 1 m cord with French plug
- "Protected" LED
- Internal safety covers protect against accidental contact with unused outlets

Specifications

OVERVIEW	
UPC Code	037332145468
INPUT	
Nominal Input Voltage(s) Supported	230V AC
Recommended Electrical Service	230V (220-250V)
Voltage Compatibility (VAC)	220-250
Input Plug Type	French
Input Cord Length (ft.)	3



Powering Business Worldwide



Right-Angle Plug	Yes
Input Cord Length (m)	0.91
Integrated Cord Clip	No
OUTPUT	
Output Receptacles	(5) French/Belgian
Circuit Breaker (amps)	10
Transformer Accommodation	(3) Yes
USER INTERFACE, ALERTS & CONTROLS	
Diagnostic LED(s)	Yes
Diagnostic LED Details	Protected
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	280
Automatic Shut-Off	No
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
PHYSICAL	
Color	Light Gray
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	No
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	12.00 x 2.17 x 4.53
Shipping Dimensions (hwd / cm)	30.48 x 5.51 x 11.51
Shipping Weight (lbs.)	0.90
Shipping Weight (kg)	0.41
Unit Dimensions (hwd / in.)	10.430 x 1.587 x 2.000
Unit Dimensions (hwd / cm)	26.49 x 4.01 x 5.08
Unit Weight (lbs.)	.87
Unit Weight (kg)	0.39
FEATURES & SPECIFICATIONS	



Powering Business Worldwide



Rotatable Outlets	No
Antimicrobial	No
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.